

## Han-Modular ECO base panel (with PE mark)



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0321
Specification	Han-Modular ECO base panel (with PE mark)
HARTING eCatalogue	<a href="https://b2b.harting.com/09140010321">https://b2b.harting.com/09140010321</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular <sup>®</sup> ECO
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With PE identification (pin 1 = PE)

### Version

Locking type	Snap-in latches
Size	Modular ECO

### Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7032 (pebble grey)
Material (seal)	NBR
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No



Pushing Performance

## Material properties

REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	EN 60664-1
	IEC 61984
CE	Yes

## Commercial data

Packaging size	2
Net weight	14.26 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140010321](#)