



Aluminum Enclosure 245x185x104mm IP67 IK09

Product Code: 402521

METEBOX - Aluminum Enclosure -External Dimensions: 250x190x110mm Internal Dimensions: 245x185x104mm IP67 IK09 ,Cover Fastening Type: Stainless Steel Screw ,Colour:Grey RAL 7040 ,Working Temperature:-40°C~+80°C ,Raw Material:Aluminum,Made in Turkey

Technical Information

Version:	
Product Name	Aluminum Enclosure
External Width (mm)	250
External Length (mm)	190
External Depth (mm)	110
Internal Width (mm)	245
Internal Length (mm)	185
Internal Depth (mm)	104
Drill hole distance vertical (mm)	236
Drill hole distance horizontal (mm)	156
Features	Drilling option is available
Cover fastening Type	Stainless Steel Screw
Technical Characteristics:	
IP	IP67
Shock Proof	IK09
Sealing	PU
Glow Wire	-
Cable Entry No.	-
Cable Entry Size	-
Included Accessories	Stainless steel screws
Module No.	-
DIN Rail	No Available
Lock Unit Number	-
Material Properties:	
Colour	Grey RAL 7040
Min-Max Working Temperature	Aluminum
Body Material	Aluminum
Cover Material	Grey - RAL 7044
Certificateion:	
Standard	TSE
Commercial Data:	
Box Quantity	8
HS CODE	8536.90.10.00.00
Country of Origin	Turkey

METE ENERJİ A.Ş.

Address:

10007 Sk. No 34 A.O.S.B 35620 Çiğli, İzmir, Türkiye
Tel: +90 (232) 376 86 86

© 2020 Mete Energy All Rights Reserved.