




3614 - FEMALE STUD, BSP PARALLEL AND METRIC



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	FKM
collar	FDA CHEMICAL NICKEL PLATED BRASS
sealing washer	FDA CHEMICAL NICKEL PLATED BRASS

Part Nb	ØD (MM)	C	E (mm)	F (mm)	H (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
3614 04 10	4	G1/8	7.5	14	25	.016
3614 04 13	4	G1/4	11	17	29	.026
3614 04 19	4	M5x0,8	5	10	22	.009
3614 06 10	6	G1/8	7.5	14	27.5	.019
3614 06 13	6	G1/4	11	17	31.5	.028
3614 08 10	8	G1/8	9.5	15	28.5	.022
3614 08 13	8	G1/4	13.5	17	32.5	.028
3614 10 17	10	G3/8	14	22	38	.052
3614 12 17	12	G3/8	14	22	39	.055
3614 12 21	12	G1/2	18.5	24	43.5	.062