


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
BT1.5I	.03 (0.8)	1.50 (38)	.041 (1.0)	.141 (3.6)	.142 (3.6)	.185 (4.7)	.248 (6.3)	6.1 (155)	40 (178)	INTERMEDIATE	.12 (56)
BT2I	.03 (0.8)	2.00 (51)	.041 (1.0)	.141 (3.6)	.142 (3.6)	.185 (4.7)	.248 (6.3)	8.0 (203)	40 (178)	INTERMEDIATE	.16 (72)
BT3I	.03 (0.8)	3.00 (76)	.049 (1.2)	.141 (3.6)	.142 (3.6)	.185 (4.7)	.248 (6.3)	11.3 (287)	40 (178)	INTERMEDIATE	.27 (121)
BT4I	.03 (0.8)	4.00 (102)	.049 (1.2)	.141 (3.6)	.142 (3.6)	.185 (4.7)	.248 (6.3)	14.3 (363)	40 (178)	INTERMEDIATE	.35 (156)
BT2S	.06 (1.5)	2.00 (51)	.045 (1.2)	.185 (4.7)	.205 (5.2)	.220 (5.6)	.320 (8.1)	8.0 (203)	50 (222)	STANDARD	.25 (113)
BT3S	.06 (1.5)	3.00 (76)	.052 (1.3)	.185 (4.7)	.205 (5.2)	.220 (5.6)	.320 (8.1)	12.0 (305)	50 (222)	STANDARD	.40 (183)
BT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.185 (4.7)	.205 (5.2)	.220 (5.6)	.320 (8.1)	15.1 (384)	50 (222)	STANDARD	.51 (230)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty CABLE TIES  
BT SERIES

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±.10(2.5) (.XXX) ±.020(.51)  
(.XX) ±.02(.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
PMH

MAT'L:

DATE  
6-24-93

NYLON 6.6

CHK'D  
JVL

SCALE  
DRAWING NO.  
BT-0037  
SHT. 2 OF 3

DWG  
A  
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
9	5/2/06	JABO		REMOVED STRAIGHT TIP REFERENCE & TIP STYLE COLUMN	0037	9		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Panduit:

[BT3I-M](#) [BT3S-C](#) [BT4S-C0](#) [BT1.5I-M0](#) [BT2I-M](#) [BT3S-M0](#) [BT2I-M30](#) [BT2S-M39](#) [BT3S-M30](#) [BT4I-C](#) [BT4S-M39](#)  
[BT2I-M69](#) [BT3S-M69](#) [BT2S-M69](#) [BT2S-M10](#) [BT4I-M14](#) [BT2S-M6](#) [BT1.5I-M7](#) [BT4S-M10](#) [BT1.5I-M5](#) [BT1.5I-M4Y](#)  
[BT1.5I-M10](#) [BT1.5I-M2](#) [BT4S-M2](#) [BT2S-M300](#) [BT1.5I-M8](#) [BT2S-M4Y](#) [BT2S-M7](#)