



## **Aluminum Enclosure 255x155x84mm IP67 IK09 with Hing**

**Product Code: 402517H**

METEBOX - Aluminum Enclosure -External Dimensions: 260x160x90mm Internal Dimensions: 255x155x84mm IP67 IK09 with Hing ,Cover Fastening Type: Stainless Steel Screw ,Colour:Grey RAL 7040 ,Working Temperature:-40°C~+80°C ,Raw Material:Aluminum,Made in Turkey

---

## Technical Information

Version:	
Product Name	Aluminum Enclosure
External Width (mm)	260
External Length (mm)	160
External Depth (mm)	90
Internal Width (mm)	255
Internal Length (mm)	155
Internal Depth (mm)	84
Drill hole distance vertical (mm)	246
Drill hole distance horizontal (mm)	126
Features	with Hing, Drilling option is available
Cover fastening Type	Stainless Steel Screw
Technical Characteristics:	
IP	IP67
Shock Proof	IK09
Sealing	PU
Glow Wire	-
Cable Entry No.	-
Cable Entry Size	-
Included Accessories	Stainless steel screws
Module No.	-
DIN Rail	No Available
Lock Unit Number	-
Material Properties:	
Colour	Grey RAL 7040
Min-Max Working Temperature	Aluminum
Body Material	Aluminum
Cover Material	Grey - RAL 7044
Certificateion:	
Standard	TSE
Commercial Data:	
Box Quantity	10
HS CODE	8536.90.10.00.00
Country of Origin	Turkey

### METE ENERJİ A.Ş.

#### Address:

10007 Sk. No 34 A.O.S.B 35620 Çiğli, İzmir, Türkiye  
Tel: +90 (232) 376 86 86

© 2020 Mete Energy All Rights Reserved.