



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC
 POLYESTER(94V-0), COLOR: BLACK
 CONTACT: COPPER ALLOY
 RETENTION LEG: PRE-TIN COPPER ALLOY

REVISONS					
P	LTR	DESCRIPTION	ECN	DATE	APVD
A		RELEASED		23AUG2005	M.M D.M
AI		ADDITION PART NO	ECR-07-005648	22MAR2007	M.M D.M



- 1. 材料:ハウジング:ガラス入り熱可塑性ポリエステル樹脂(94V-0)、色:黒
 コンタクト:銅合金
 リテンションレグ:錫めっき銅合金
- 2. めっき:全面:ニッケル下地めっき1.27μm以上
- 3. めっき:接触部 2の上に金めっき0.38μm以上
- 4. めっき:コンタクト半田付部: 2の上に錫めっき2μm以上
- 5. 文字の形状、大きさ、および位置については、大略を示すものであり、
 詳細を示すものではありません。
- 6. Y KEY形状は、X KEY形状と左右対称

- 2. FINISH(ALL OVER):NICKEL PL. 1.27μmMIN
- 3. FINISH(CONTACT AREA):GOLD PL. 0.38μmMIN AFTER 2
- 4. FINISH(CONTACT TAIL):TIN PL. 2μmMIN AFTER 2
- 5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
- 6. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".



RECOMMEND PC BOARD HOLE PATTERN
 : CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
 PC BOARD THICKNESS : 1.0~1.6±0.1

推奨基板取付穴寸法:コネクタ搭載面(非累積公差)
 PC基板厚:1.0~1.6±0.1












40	Y	19	38.0	41.0	42.6	2-1827872-0
40	X	19	38.0	41.0	42.6	1-1827872-0
34	Y	16	32.0	35.0	36.6	2-1827872-7
34	X	16	32.0	35.0	36.6	1-1827872-7
32	X	15	30.0	33.0	34.6	1-1827872-6
30	X	14	28.0	31.0	32.6	1-1827872-5
28	X	13	26.0	29.0	30.6	1-1827872-4
26	X	12	24.0	27.0	28.6	1-1827872-3
22	X	10	20.0	23.0	24.6	1-1827872-1
POS KEY	n		A	B	C	PART NO

40POS(X-KEY): 1-1827872-0

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN T. KUDO 16MAR2005	Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位: 純 mm		CHK D. MITSUGI 23AUG2005	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 22-40POS	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±3° 0-PLC ± 1-PLC ±0.3 2-PLC ±0.10 3-PLC ±0.001 4-PLC ±0.0001 ANGLES ± FINISH 仕		APVD D. MITSUGI 23AUG2005	PRODUCT SPEC 108-78268	
MATERIAL 材料		APPLICATION SPEC 取付適用規格 114-5377	SIZE A2	
		WEIGHT -	CAGE CODE 00779	
		DRAWING NO 1827872		RESTRICTED TO -
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 3

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
J	-	P	LTR	DATE	DWN	APVD
				DESCRIPTION		
				SEE SHEET 1 OF 3		



22POS(X-KEY): 1-1827872-1







26POS(X-KEY): 1-1827872-3

28POS(X-KEY): 1-1827872-4

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN T. KUDO 16MAR2005 CHK D. MITSUGI 23AUG2005 APVD D. MITSUGI 23AUG2005	tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 1. PLC ± 2. PLC ± 3. PLC ± 4. PLC ± ANGLES ± FINISH	PRODUCT SPEC 108-78268 APPLICATION SPEC 114-5377 WEIGHT -	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 22-40POS SIZE A2 CAGE CODE 00779 DRAWING NO. 1827872 RESTRICTED TO -
MATERIAL -		CUSTOMER DRAWING	SCALE 4:1 SHEET 2 OF 3 REV A1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1 OF 3			



32POS(X-KEY): 1-1827872-6

34POS(X-KEY): 1-1827872-7

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN T. KUDO 16MAR2005 CHK D. MITSUGI 23AUG2005 APVD D. MITSUGI 23AUG2005	tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan
DIMENSIONS: mm	TO DRAWING'S UNLESS OTHERWISE SPECIFIED: 1. PLC ± - 2. PLC ± - 3. PLC ± - 4. PLC ± - ANGLES ± - FINISH	PRODUCT SPEC 108-78268 APPLICATION SPEC 114-5377 WEIGHT -	NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY (V-TYPE) 22-40POS SIZE A2 CAGE CODE 00779 DRAWING NO. 1827872 RESTRICTED TO -
MATERIAL -		CUSTOMER DRAWING	SCALE 4:1 SHEET 3 OF 3 REV A1