



412 - Cable cutters



Description:

- 412B.10 "Compact" cable cutters: - Capacity: diameter 10 mm. - Integral opening spring. - Lock closed catch. - Cross proof design.
- 412.16 "Standard" cable cutters: - Capacity: diameter 16 mm. - Heavy-duty head, cross proof design. - Safety stop.
- 412.30 - 412.42 "Heavy-duty" cable cutters: - Capacity: 32 mm (Ref. 412.30) and 42 mm (Ref. 412.42).
- Powerful action, cuts without crushing electric cables..
- Safety stop.
- Set of blades for 412.30: 412.L30.
- Set of blades for 412.42: 412.L42.



	Diameter [mm]	Diameter D Mini - Maxi [mm]	Length L [mm]	Length L1 [mm]	Thickness E [mm]	Head Height C [mm]	Head Width B [mm]	Weight [Kg]
412.16	16.0	80 - 370	290.0	45.0	14.0	28.0	54.0	0.67
412.30	32.0	155 - 1000	600.0	60.0	16.0	40.0	70.0	2.5
412.42	42.0	200 - 1300	800.0	90.0	16.0	70.0	115.0	3.7
412B.10	10.0	53 - 190	170.0	40.0	10.0	21.0	28.0	0.225