


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm ²]	HOUSING COLOR	DIMENSIONS in. [mm]					WIRE STRIP LENGTH in [mm] +1/32 [0,8] -0	TOOLS
			L ± .04 [1,1]	B ± .01 [0,3]	C ± .01 [0,3]	T ± .01 [0,3]	MAX. WIRE INSUL. DIA.		
EDV18-87MB	#22-18 [0,5-1,0]	RED	1.10 [28,0]	.087 [2,2]	.71 [18,0]	.030 [0,75]	.145 [3,7]	9/32 [6,8]	KST-2000A
EDV14-87MB	#16-14 [1,5-2,5]	BLUE	1.10 [28,0]	.087 [2,2]	.71 [18,0]	.031 [0,80]	.165 [4,2]		
EDV10-11MB	#12-10 [4,0-6,0]	YELLOW	.91 [23,0]	.110 [2,8]	.39 [10,0]	.039 [1,0]	.240 [6.1]	11/32 [8,8]	

NOTES:

- UL LISTED FOR:
 - A. SOLID OR STRANDED COPPER WIRE ONLY
 - B. 221°F [105°C] MAX OPERATING TEMPERATURE
 - C. 600V MAX VOLTAGE RATING
- MATERIAL:
 - A. STAMPING: COPPER, TIN PLATED
 - B. HOUSING: VINYL
- SEE WWW.PANDUIT FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



TITLE					STRONGHOLD BLADE TERMINAL VINYL INSULATED, BUTTED SEAM #22-10 AWG CUSTOMER DRAWING																													
ITEM REVISION NAME					00123SSC/00																													
DATASET FILE NAME					00123SSC_DC/00																													
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					MATERIAL:																													
.x ± .1 [2.54] .xx ± .01 [.25]					.xxx ± .005 [.127] ANGLES ± 5°																													
DRAWN BY					DAW																													
DATE					-																													
CHK					-																													
SCALE					N.T.S.																													
DRAWING NUMBER:					00123SSC-DC																													
REV					DATE					BY					CHK					APR					DESCRIPTION					ECN				
00					2/18					JHNU					TMR					RGB					DRAWING RELEASED					00123SS				
SHEET 1 OF 1					A																													

D10100DA/12

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[EDV10-11MB-Q](#) [EDV14-87MB-Q](#) [EDV18-87MB-Q](#)