

Han GND hood, 7,5-14mm




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0430
Specification	Han GND hood, 7,5-14mm
HARTING eCatalogue	https://b2b.harting.com/09140010430

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] GND
Type of hood/housing	Hood

Version

Locking type	Snap-in latches
Version	Top entry
Cable entry	1x Integrated

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
Cable diameter	7.5 ... 14 mm

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Green Yellow
Material (seal)	NBR
Material (cable glands)	Polyamide (PA)
Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	39.8 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09140010430](#)