

E.306A - Electronic torque wrenches with ratchet




Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Accuracy: $\pm 2\%$ between 20% and 100% wrench capacity.
- Measuring mode: peak or follower.
- Measuring unit: N.m, lbf.ft, lbf.in and kg.cm.
- Bits: 9 x 12 and 14 x 18 mm.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Presetting possible of 9 torque and/or angle values.
- Memory 250 values with PC USB link.
- Supplied in plastic case with foam interior.

	Capacity [Nm]	Square [in]	Weight [Kg]	Ratchet ["]
E.306A135J	6.7 - 135	3/8	1.7	J.372V
E.306A135S	6.7 - 135	1/2	1.7	S.372V
E.306A200S	10 - 200	1/2	2.7	S.382V
E.306A30R	1.5 - 30	1/4	1.6	R.372
E.306A340S	17 - 340	1/2	2.9	S.382V