


229A - Stepped bits



Description:

- For cylindrical high accuracy drilling in all materials.
- HSS steel.
- Cylindrical shank with 3 flats for proper drive, avoiding micro locking.
- Laser marking of different diameters in a groove.



	Diameter D Mini - Maxi ["]	Diameter D1 [mm]	Length L [mm]	Weight [g]
229A.ST0			65.0	25.0
229A.ST1	4 - 6 - 8 - 10 - 12 - 14 - 16 - 18 - 20	8.0	75.0	65.0
229A.ST2	4 - 6 - 9 - 12 - 15 - 18 - 21 - 24 - 27 - 30 - 33 - 36 - 39	10.0	107.0	315.0
229A.ST3	6 - 9 - 13 - 16 - 19 - 21 - 23 - 26 - 29 - 32 - 35 - 38	10.0	100.0	320.0