



271A - Compact G-clamp



Description:

- Capacity: 0 to 250 mm and 0 to 9"7/8.
- Presentation: galvanised - burnished screw.



	Length L [mm]	Length L1 [mm]	Length L2 [mm]	open position o maxi [mm]	A Maxi [mm]	Weight [Kg]
271A.100	192	131.0	77.0	100.0	100	
271A.120	223.0	148.0	88.0	120.0	120.0	1.68
271A.150	262.0	162.0	98.0	150.0	150.0	1.98
271A.200	320	185.0	108.0	200.0	200	
271A.250	380	202.0	118.0	250.0	250	
271A.40	100.0	75.0	42.0	40.0	40.0	0.3
271A.60	130.0	98.0	57.0	60.0	60.0	0.51
271A.80	167.0	115.0	67.0	80.0	80.0	0.81