



0.2m USB 2.0 Type A to Micro-B Cable, Anthra

Line

No.: 36730

USB Type A Male to Micro-B Male

Description

- Professional choice USB 2.0 Type A to Micro-B cable for commercial and high performance AV and IT installations
- Supports data transfer speeds up to 480Mbps
- Robust PVC housing, nickel connectors and gold plated contacts
- Double shielded cable, corrosion resistant tinned copper conductors
- USB 2.0, 480Mbps; 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Anthra Line USB 2.0 Type A to Micro-B cables are the professional choice for high performance connections in commercial AV and IT installations.

Anthra Line USB 2.0 cables are premium connections that feature double shielded construction with copper conductors for performance and corrosion resistance. High quality gold plated contacts and nickel connectors maintain signal integrity and reliability.

Data transfer speeds up to 480Mbps are supported for the quick and effortless transfer of large data volumes.

Anthra Line USB 2.0 Type A to Micro-B cables are available in lengths from 0.2m, 0.5m, 1m, 2m, 3m and 5m

Technical details

Connectors

- Connector A: USB 2.0 Type A Male
- Connector B: USB 2.0 Type Micro-B Male
- Housing Material: PVC
- Connector Plating: Nickel
- Pin Construction: Copper
- Pin Plating: Gold
- Dimensions (approx.) WxDxH:
 A: 15.5x35x7.8mm (0.61x1.38x0.31in)
 - Micro-B:10x24x7.6mm (0.29x0.95x0.30in)

Cable Construction

- Length: 0.2m (0.66ft)
- Standard: USB 2.0

- Colour: Black
 Type: Round
 Jacket Diameter: 3.5mm (0.14in)
 Jacket Material: PVC

- Conductor Material: Tinned Copper
 Conductor Gauge: 28/28AWG
 Shielding: Aluminium Magnesium Braid

Specifications

- Supported Bandwidth: 480Mbps
 Maximum Resolution: Nominal Attenuation: 5.8db/km

- Minumum Band Radius: 16mm (0.63in)
 Operating Temperature: 0°C 60°C (32°F 140°F)
 Storage Temperature: 0°C 60°C (32°F 140°F)
 ATC Approved: -

Miscellaneous

- Packaging Type: Polybag
 Warranty (Years): 10
 Certificated: RoHS, REACH & UL

Purchasing Information

- No.: 36730EAN: 4002888367301

This product is also available in other lengths

- 36730 0.2m (0.66ft)
- 36731 0.5m (1.64ft)
- 36732 1m (3.28ft)
- 36733 2m (6.56ft)
- 36734 3m (9.84ft)
- 36735 5m (16.44ft)

© LINDY 2020