

Click wrenches with removable ratchet




Standards:

NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

Description:

- Factory accuracy: $\pm 4\%$.
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Can be used with $\varnothing 30$ mm accessories.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrench supplied with ISO 6789 calibration certificate.
- Supplied in plastic box with ratchet.

	Length L [mm]	Attachement [mm]	Capacity [Nm]	Graduation [Nm]	Ratchet ["]	Weight [Kg]
K.306A1000	1280.0	$\varnothing 30$ mm	200 - 1000	4.0	K.151A	5.9