

FEATURES

- The body is available in burnished steel with black oxide finish or stainless steel
- Hardened plunger
- Knob material high impact resistant thermoplastic
- Knob finish matt
- Standard colour black knob
- Comes at standard with 90° locking rest position in plunger body

RS PRO M16 Index Plunger, 75.5mm Long

RS Stock No.: 478-769



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description ATTRIBUTE

These spring-loaded hand retractable plungers from our own RS PRO brand are designed to prevent any change in locking position due to lateral force. Pulling up on the handle retracts the plunger pin into the body

General Specifications

Туре	Index Plunger				
Body Material	Burnished steel				
Thread Size	M16				
Applications	Ideal for applications where precision positioning is needed, such as rotary indexing heads. Clamping of adjustable elements; Positioning of work pieces; Latching of mechanisms				
Rest Position	No				

Mechanical Specifications

Length	75.5mm
Ball Diameter	8mm


Approvals

Compliance/Certifications	RoHS
---------------------------	------

Ball & Spring Plungers







Part No.	Α	В	С	D	E	Thread size	Plunger diameter (mm)	Rest position
478359	21	51	5	17	5	M10x1.0	5	No
237491	25	45	5	10	6	M12x1.5	6	No
478721	25	61	6	20	6	M12x1.5	6	No
237429	31	54	6	12	8	M16x1.5	8	No
478769	31	75	8	26	7	M16x1.5	8	No
237570	25	45	5	10	6	M12x1.5	6	Yes
237388	31	54	6	12	8	M16x1.5	8	Yes