


## Tripp Lite Waber Industrial Power Strip, 6-Outlet, 6 ft. (1.83 m) Cord

MODEL NUMBER: 6NX6



### Highlights

- 6 outlets
- 6-ft. (1.83 m) cord
- 12.5-in. length
- Master on/off switch
- All-metal housing

### Package Includes

- 6NX6 Power Strip
- Warranty information
- Instruction manual

### Description

Tripp Lite's 6NX6 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing, 6-ft. (1.83 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 6NX6 ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige housing with black receptacles. PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R  
 ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)  
 FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation on a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-ft. (1.83 m) AC line cord

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332107107 |
| INPUT    |              |



|   |  |
|---|--|
| Nominal Input Voltage(s) Supported                | 120V AC                                      |
| Recommended Electrical Service                    | 15A 120V                                     |
| Voltage Compatibility (VAC)                       | 120  |
| Input Plug Type                                   | NEMA 5-15P                                   |
| Input Cord Length (ft.)                           | 6  |
| Input Cord Length (m)                             | 1.83   |
| Integrated Cord Clip                              | No   |
| <b>OUTPUT</b>                                     |  |
| Frequency Compatibility                           | 50 / 60 Hz                                   |
| Output (Watts)                                    | 1800   |
| Output Receptacles                                | (6) 5-15R                                    |
| Circuit Breaker (amps)                            | 15   |
| Transformer Accommodation                         | (2) Yes                                      |
| Outlet Orientation                                | Single row of 6                              |
| Right-Angle Outlets                               | No   |
| Outlet Spacing                                    | 1.520 in.                                    |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b>      |  |
| Switches  | Lighted combination switch / circuit breaker |
| <b>PHYSICAL</b>                                   |  |
| Color   | Beige  |
| Material of Construction                          | Metal  |
| Antimicrobial                                     | No   |
| Power Cord Color                                  | Black  |
| Housing Color                                     | Beige  |
| Mounting Holes or Slots                           | Yes  |
| Slot or Hole Mount Measurement (Center to Center) | 240mm  |
| Outlets Measurement (Center to Center)            | 75.9mm                                       |
| Receptacle Color                                  | Black  |
| Shipping Dimensions (hwd / cm)                    | 36.07 x 6.60 x 15.49                         |
| Shipping Dimensions (hwd / in.)                   | 14.20 x 2.60 x 6.10                          |
| Shipping Weight (kg)                              | 0.73   |
| Shipping Weight (lbs.)                            | 1.60   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                           |
|-------------------------------------|---------------------------|
| Unit Dimensions (hwd / cm)          | 31.75 x 6.35 x 3.8        |
| Unit Dimensions (hwd / in.)         | 12.5 x 2.5 x 1.5          |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Canada                              | cUL                       |
| UL1363 (Power Tap)                  | UL1363                    |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>