



2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NO.	MAX. COMBINED BUNDLE DIA. D1 + D2 in (mm)	A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MIN. LOOP TENSILE lbs (N)	CROSS-SECTION	WEIGHT lbs/100pcs (g)
PLB2S	1.8 (45.7)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.320 (8.1)	7.6 (193)	50 (222)	STANDARD	.34 (154)
PLB3S	3.0 (76.2)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.337 (8.6)	11.8 (300)	50 (222)	STANDARD	.47 (214)
PLB4S	4.1 (104.1)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.337 (8.6)	14.8 (376)	50 (222)	STANDARD	.58 (262)

* SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR

D10100DA/16

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
6	11.20.14	BDK	MPH	JADE	UPDATED TITLE BORDER AND UPDATED NOTES	SS-21645	KEM	4/6/87	HVP	NONE	SHT 1 OF 1	A

TITLE
**BOW-TY CABLE TIES
PLB SERIES**
CUSTOMER DRAWING

ITEM REVISION NAME
10B0150W/00

DATASET FILE NAME
10B0150W_DC_PLB/00A

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.x ± .xxx ± .020 [.51]
.xx ± .02 [.5] ANGLS ±

MATERIAL:
NONE

DRAWING NUMBER:
SS-21645

THIRD ANGLE PROJECTION

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PLB3S-C0](#) [PLB4S-C](#) [PLB4S-M](#) [PLB4S-M30](#) [PLB4S-M39](#) [PLB4S-M0](#)