

Pushbutton, 15.2 mm, quick connector, momentary contact function, 1 NC, bezel red



fields of application

- > Mechanical and system engineering
- > Model construction
- > Home technology

special features

Drucktaster opak, nicht beleuchtbar
 Einbaudurchmesser 15,2, mm
 max. 250 V / 700 mA
 Schraub- oder Flachstecker-Anschluss
 Befestigungstechnik mit Gewinding
 Schutzart IP 40 frontseitig (IP 65 mit Schutzkappe)



description

Pushbutton with mounting hole diameter 15.2 mm

Pushbutton with mounting hole diameter 15.2 mm, solder/quick-connect terminal for 6.3 x 0.8 mm or 2 x 2.8 x 0.8 mm

technical data

> general

| | |
|---|-------------------------------|
| Bezel color | red |
| Property of bezel / mushroom | opaque |
| Collar shape | round |
| Operating temperature, min. | -25 °C |
| Operating temperature, max. | 85 °C |
| Storage temperature, min. | -40 °C |
| Storage temperature, max. | 90 °C |
| illuminated | No |
| Packaging | Box |
| Packaging unit | 100 pcs. |
| net weight | 5.6 g |
| Operating life | 25,000 cycles |
| B10 | 32,500 cycles |
| Degree of protection, front side, according to DIN EN 60529 | IP40 IP65 with sealing cap |
| MOQ order | 100 pcs. |
| RoHS compliant | Yes |
| REACH compliant | Yes |

direct links

> [RAFI eCatalog](#)

> mounting diameters

| | |
|---------------------------|---------|
| Outside dimension, length | 19 mm |
| Outside dimension, width | 19 mm |
| Outside dimension, height | 29.7 mm |
| Mounting hole | 15.2 mm |

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which may change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

date: Feb 23, 2024 page: 1/2

RAFI GmbH & Co. KG

Ravensburger Str. 128-134
 88276 Berg / Ravensburg
 Germany
www.rafi-group.com,
info.headquarters@rafi-group.com

| | |
|-----------------------------|---|
| Mounting depth | 21.5 mm |
| Installation height | 8.2 mm |
| > mechanical data | |
| Actuation function | momentary contact function |
| Operating force, max. | 7.5 N |
| Operating travel, max. | 3 mm |
| Contact function | 1 NC |
| Contact system | Bridge contact |
| Contact material | Silver |
| Fixing | Threaded ring |
| Solderability | No |
| Terminal on the rear | Flat quick-connect terminal 6.3 x 0.8 / 2 x 2.8 x 0.8 |
| > electrical data | |
| Rated voltage, max. | 250 V |
| Rated current, max. | 0.7 A |