



+ CABLE ASSEMBLIES

PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

TE CONNECTIVITY (TE)

C/A, SFP+, GENERIC, 1.0M

SFP+ | SFP+

2127931-2

TE Internal Number: 2127931-2

EU RoHS Compliant

EU ELV Compliant

Cable Assembly Type Small Form Factor Pluggable (SFP)

Equalized No

Wire Size (AWG) 30

Wire Size (mm²) .051

Shielded Yes

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

CABLE ASSY,30 AWG,SFP+ TO SFP+ NI_PLATED

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

4-1773455-3 - Quick Reference Guide SFP+ Solutions

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Assembly Category High Speed

Cable Assembly Type Small Form Factor Pluggable (SFP)

Shielded Yes

Connector Type (End A) SFP+

Connector Type (End B) SFP+

Cable Style Madison TurboTwin - Round Jacketed, Madison TurboTwin

Product Designation Patch Cord

Product Type Cable Assembly

Latching Style Retractable Pin

Configuration Features

Number of Positions 2-Pair

Number of Power Positions 0

Number of Signal Positions 4

Keyed No

Configuration Double-Ended

Electrical Characteristics

Impedance (Ω) 100

Signal Characteristics

Data Rate (Gb/s) 10

Body Features

Jacket Material Flexible PVC

Equalized No

Color Black

Shield Material Aluminum/Polyester/Aluminum Tape/Tin-Plated Copper Braid

Strain Relief Type Overmold

Release Type Pull Tab

Contact Features

Contact Mating Area Plating Material Gold

Mechanical Attachment

Jackscrew Without

Housing Features

Housing Material Zinc Alloy

Dimensions

Wire Size (AWG) 30

Wire Size (mm²) .051

Industry Standards

IEEE 1394 No

Other

Cable Assembly Length 1 m [3.281 ft]

CLOUDSPLITTER No

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
