
Resin finger guards Dimensions (unit: mm)

Material Frame: Resin (PPE+PS) UL file no. E82268 94V-0


92 mm sq. type

Model no.	Mass (g)
109-1001G	12



Airflow - Static pressure characteristics

Measured with our double chamber measuring device (120 mm sq. type)



Applied voltage: 12 VDC

* Finger guard is attached on air inlet side of fan.

●Operating temperature limit is between -20 to +70°C. (non condensing)

•Plastic finger guards are placed on both the intake and exhaust sides of the fan.

•No nuts or screws for use in attachment included.

DC AC

Mounting example

