

# 0 601 8B5 001 – GOP 12V-28

Material number	0 601 8B5 001
EAN	3165140842501
1 x Starlock BIM plunge cut saw blade AIZ 32 APB, Wood + Metal, Curved-Tec 2 608 661 644	✓
Carton L-BOXX-ready	✓
L-BOXX 136 1 600 A00 1RR	
Weight incl. battery	1,0 kg



## Technical data

### Technical data

Battery voltage	12 V
Battery capacity	2,0 Ah 2,5 Ah 3,0 Ah 4,0 Ah
No-load rotation	5.000 – 20.000 opm
Oscillation angle on left and right	1,4 °
Length	285 mm
Width	51 mm
Height	84 mm
Weight excl. battery	0.81 kg



### Noise/vibration information

Sound pressure level	79 dB(A)
Sound power level	90 dB(A)
Uncertainty K	3 dB
Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level 79 dB(A); Sound power level 90 dB(A). Uncertainty K= 3 dB.

## Sales information

### Positioning

- The most compact problem-solver in the Starlock range

### User benefit

- Higher power transmission between tool and accessory due to 3D Starlock Interface
- Best ergonomics due to the smallest gripping circumference in the market
- Ease of use thanks to interface with magnetic mounting support