

# Power Inlet with Filter

## FEATURES:

- Compact structure
- Convenient installation
- High cost performance

## SPECIFICATION:

Depth	58 mm
Height	22.8 mm
IEC-climate category	25/085/21
Leakage current	0.6 mA @ 250VAC/50Hz
Rated current	6 A
Rated voltage	250 VAC
Max. temperature	+85 °C
Min. Temperature	-25 °C
Resistance	50 MΩ
Width	50 mm
Termination type	Snap-In, Soldering Lugs
Inlet type	C14

## Art. Nr.

**RND 165-00034**

