



MALE END VIEW	
1 3	
enna fost,	

SPECIFICATIONS		
CONTACT MATERIAL/PLATING	BRASS/GOLD	
HOUSING MATERIAL/PLATING	BRASS/NICKEL	
RATED CURRENT [A]	4.0 A	
RATED VOLTAGE [V]	250 V	
MAXIMUM WIRE SIZE	20 AWG	
CABLE GRIP RANGE	6-8mm	
TEMPERATURE RATING	-40°C to +85°C (-40°F to +185°F)	
PROTECTION CLASS	IEC IP67	
WIRE TERMINATION	SCREW TERMINAL	









SOURCE DRAWING - FOR REFERENCE ONLY

