SPECIFICATIONS


(RoHS Compliant)

Model Number: SD48B1

Part Number: 19028935A SPEC Number: 26013993A01 Jan.01.2013



Mechanical Drawing:



Motor:

Nominal Voltage =48 vdcOperating Voltage Range = 24 - 56 vdcNominal Running Current = 0.060 ampsLocked Rotor Current = 0.300 amps**Running Power** = 3.0 watts Average Speed = 3500**Bearings** = BallAirflow = 35 CFMAcoustic $= 47.6 \, dBA$

Construction:

Venturi: One Piece Die-Cast Zinc Alloy, Black

Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 83,000

hours at 40°C

Additional Features:

Brushless DC Motor Locked Rotor Protection Automatic Restart Capability

Polarity Protected

Operating temperature: -10°C to 70°C Storage Temperature: -40°C to 85°C

Termination:

12" leadwires, AWG 22, UL 1061

Red: = Power (+) Black: = Return (-)

Agency Approvals:

UL, CE