

Uni-Dicht-Verschraubung Pg36, 29-34mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5098
Specification	Uni-Dicht-Verschraubung Pg36, 29-34mm
HARTING eCatalogue	https://b2b.harting.com/09000005098

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Limiting temperature	-40 ... +130 °C
Tightening torque	≤30 Nm (depending on the cable and the seal insert used)
Wrench size	50
Degree of protection acc. to IEC 60529	IP68
Size	Pg 36
Clamping range	29 ... 34 mm

Material properties

Material (cable glands)	Metal
Colour (accessories)	Light blue
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance

Commercial data

Packaging size	1
Net weight	151.75 g
Country of origin	Germany
European customs tariff number	84849000
eCl@ss	27144432 Screwed cable gland (electr.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09000005098](#)