


# DIP Ribbon Cable Plug 16P



## FEATURES:

### SPECIFICATION:

Poles	16
Pitch	2.54 mm
Rated current	1 A
Housing Material	Glass fibre (GF)/Polybutylene terephthalate (PBT)
Contact material	Copper alloy
Test voltage	0.5 kV
Temperature range	-40...+105 °C
Combustibility class	UL 94 V-0
A	25.77 mm
B	19.05 mm
C	17.78 mm



**Art. Nr.**  
**RND 205-00693**

