

Power Inlet with Filter

FEATURES:

Compact structure
 Convenient installation
 High cost performance

SPECIFICATION:

Rated voltage	250 VAC
Rated current	4 A
Depth	54.5 mm
Dimensions H x W x D	31.3 x 44 x 54.5 mm
Leakage current	0.6 mA@ 250VAC/50Hz
Resistance	50 MΩ
Temperature range	-25 ... +85 °C
Termination typ	Snap-In/Soldering Lugs
Inlet type	C14

Art. Nr.

RND 165-00115

