




249.G4 249G - Sheathed drift punches



- Long shank.
- Head hardened to 43 HRc.
- Shank hardened to 58 HRc.

A [mm]: 3,95

d [mm]: 10

L [mm]: 190

L1 [mm]: 60

L2 [mm]: 105

[g]: 94

[kg]: 0,094