

## GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000
Unit	Trade / Industry
Type	Angle, concrete grinder (electric)
Status	Ok
Creation date	2018-07-25 simon.fischer
Last date modified	2018-12-14 simon.fischer



### Assigned Categories

Category Path	OCS / Professional Power Tools / Angle grinders & metalworking
Leaf-Category	Small angle grinders 500 W-1900 W
Category Path	OCS / Professional Power Tools
Leaf-Category	Heavy Duty
Category Path	OCS / Trade/industry / Angle grinders & metalworking
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry Subsections / Construction / Angle grinders & metalworking
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry Subsections / Electrician / Angle grinders & metalworking
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry Subsections / Metal construction / Angle grinders & metalworking
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry Subsections / Plumbing, heating and air conditioning technology / Angle grinders & metalworking
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry / New tools
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry Subsections / Construction / New tools
Leaf-Category	Small angle grinders with X-LOCK



# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## Assigned Categories

Category Path	OCS / Trade/industry Subsections / Electrician / New tools
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry Subsections / Metal construction / New tools
Leaf-Category	Small angle grinders with X-LOCK
Category Path	OCS / Trade/industry Subsections / Plumbing, heating and air conditioning technology / New tools
Leaf-Category	Small angle grinders with X-LOCK

## Administrative information

Proofreading done	<input checked="" type="checkbox"/>
maintained by	maintained by BI
Mailing allocation	• Metall

## Release

PM responsible	Simon Fischer
----------------	---------------

## Visible for the following regions

REA	<input checked="" type="checkbox"/>
REE	<input checked="" type="checkbox"/>
RMI	<input checked="" type="checkbox"/>



# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## Description

Trades	<ul style="list-style-type: none"><li>• Construction</li><li>• Electrician</li><li>• Metal construction</li><li>• Plumbing, heating and air conditioning technology</li></ul>
Product category subdivision	Angle Grinder
Positioning	Superior tool control with improved power level in 900 W category - with X-LOCK
Long version part 1	The GWX 9-115 S Professional corded small angle grinder with X-LOCK delivers superior tool control while reaching new power levels in the 900 W category. Its powerful 900 W motor facilitates fast work progress. This small angle grinder comes with a keyless X-LOCK click system that enables fast and convenient accessory changes. Furthermore, its speed selection feature produces perfect working results in a variety of materials and with a wide range of accessories. This tool is intended for cutting and grinding metal, tiles, and bricks.
Long version part 2	The GWX 9-115 S Professional also features a protection guard and restart protection.
User benefit incl. Reason to believe	<ul style="list-style-type: none"><li>• Small angle grinder with powerful 900 W motor for fast work progress</li><li>• Changing accessories is fast and convenient thanks to keyless X-LOCK click system</li><li>• Speed selection feature produces perfect working results in a variety of materials and with a wide range of accessories</li></ul>
Short version additional information	Also features protection guard and restart protection
First SOL	2019-02-15

## Technical data

Rated input power [W]	900
No-load speed [rpm]	2.800 – 11.000
Power output [W]	450
Disc diameter [mm]	115
Rubber backing pad, diameter [mm]	115
Wire cup brush, diameter [mm]	75
Tool dimensions (width) [mm]	73
Tool dimensions (length) [mm]	280
Tool dimensions (height) [mm]	100

# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## Technical data

Tool dimensions (width x length x height) [mm]	73 x 280 x 100
Weight [kg]	2,1
Switch	2-way

## Noise/vibration information

Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level 93 dB(A); Sound power level 104 dB(A). Uncertainty K= 3 dB.
-------------	---

## Linked products










Matching-Code	<ul style="list-style-type: none"><li>• Diamond drilling   Mains-powered dry   X-LOCK (only X-LOCK angle grinders)</li><li>• Diamond cutting   X-LOCK Angle grinders   Outer diameter 115 mm, Inner diameter 22.23 mm</li><li>• Sanding   X-LOCK Angle grinders   Fibre sanding disc / flap disc 115 mm x 22.23 mm</li><li>• Sanding   X-LOCK Angle grinder   115 mm</li><li>• Wire brushes   X-LOCK Angle grinders   X-LOCK</li><li>• Grinding   X-LOCK Angle grinders   Bore 22.23 mm   Outer diameter 115 mm</li><li>• Cutting   X-LOCK Angle grinders   Bore 22.23 mm   Outer diameter 115 mm</li></ul>
Areas of application	<ul style="list-style-type: none"><li>• Cutting concrete</li><li>• Cutting ferrous metals</li><li>• Cutting wood</li><li>• Cutting synthetic material</li><li>• Cutting non-ferrous metal</li><li>• Cutting stone</li><li>• Sanding ferrous metals</li><li>• Sanding non-ferrous metal</li><li>• Brushing coating material</li><li>• Brushing ferrous metals</li><li>• Brushing non-ferrous metal</li><li>• Dry drilling in stone</li></ul>



# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## Linked digital objects

<p>Operating Instructions, Western Europe</p>  <p>1 609 92A 4FA_1901 Object ID: #296898</p>	<p>Product image</p>  <p>GWX_9-115_S_dyn Object ID: #285464</p>	<p>Symbol image</p>  <p>verdrehsichereSchutzhaube Object ID: #27716</p>	<p>Symbol image</p>  <p>X- Object ID: #260067</p>	<p>Symbol image</p>  <p>BoschWorldsFirst-HR Object ID: #214387</p>
<p>Symbol image</p>  <p>Ergonomic_GSS Object ID: #162479</p>	<p>Symbol image</p>  <p>Electronic_Picto_GW Object ID: #5781</p>	<p>Symbol image</p>  <p>Bosch_BI_Icon_Restart- Object ID: #236057</p>	<p>Dimensional drawing</p>  <p>GWX_9-115_S_stat Object ID: #293595</p>	

## CSO selection 1

Order No.	0 601 7B1 000
EAN-Code	3165140962537
maintained by	maintained by BI
Product Name	GWX 9-115 S
Title	Angle Grinder GWX 9-115 S Professional
New for OCS/Print	☑
New for OCS/Print until	15.08.2019
Baretool number	• 3601GB1000

# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## CSO selection 1

Scope of supply	<ul style="list-style-type: none"><li>• Auxiliary handle (spare part number 2 602 025 067)</li><li>• Carrying case (1 619 P06 556)</li><li>• Protective guard (2 608 000 677)</li></ul>
SOL Date	15.02.2019
HD SKU	☑
Packaging dimensions (width x length x height) [mm]	310 x 450 x 120
Voltage, electrical [V]	230
Voltage range [V]	220 – 240
Speed control	☑
Protective guard with quick adjustment	☑
Vibration Control auxiliary handle	☑

## Linked Digital Objects

Product image, scope of delivery



GWX\_9-115\_S\_SOS\_0-  
Object ID: #295300

## CSO selection 2

Order No.	0 601 7B1 060
EAN-Code	3165140962544
maintained by	maintained by BI

# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## CSO selection 2

Product Name	GWX 9-115 S
Title	Angle Grinder GWX 9-115 S Professional
New for OCS/Print	☑
New for OCS/Print until	15.08.2019
Baretool number	• 3601GB1060
Scope of supply	• Auxiliary handle (spare part number 2 602 025 067) • Cardboard box • Protective guard (2 608 000 677)
SOL Date	15.02.2019
HD SKU	☑
Packaging dimensions (width x length x height) [mm]	160 x 320 x 160
Voltage, electrical [V]	110
Speed control	☑
Protective guard with quick adjustment	☑
Vibration Control auxiliary handle	☑

## Linked Digital Objects

Product image, scope of delivery



GWX\_9-115\_S\_SOS\_0-  
Object ID: #295301

# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## CSO selection 3

Order No.	0 601 7B1 070
EAN-Code	3165140962551
maintained by	maintained by BI
Product Name	GWX 9-115 S
Title	Angle Grinder GWX 9-115 S Professional
New for OCS/Print	☑
New for OCS/Print until	15.08.2019
Baretool number	• 3601GB1070
Scope of supply	<ul style="list-style-type: none"><li>• Auxiliary handle (spare part number 2 602 025 067)</li><li>• Cardboard box</li><li>• Protective guard (2 608 000 677)</li></ul>
SOL Date	15.02.2019
HD SKU	☑
Packaging dimensions (width x length x height) [mm]	120 x 360 x 120
Voltage, electrical [V]	230
Voltage range [V]	220 – 240
Speed control	☑
Protective guard with quick adjustment	☑
Vibration Control auxiliary handle	☑



# GWX 9-115 S

Internal ID	#47402
Master-Order-No.	0 601 7B1 000

## Linked Digital Objects

Product image, scope  
of delivery



GWX\_9-115\_S\_SOS\_0-  
Object ID: #295301