

## Detailed Specifications

<b>Frame Width:</b>	38[mm]
<b>Frame Height:</b>	38[mm]
<b>Frame Depth:</b>	28[mm]
<b>Max. Air Flow:</b>	21.4[CFM]
<b>Max. Air Flow:</b>	0.61[m <sup>3</sup> per min]
<b>Max. Static Pressure:</b>	2.61[In H <sub>2</sub> O]
<b>Max. Static Pressure:</b>	650[Pa]
<b>Fan Speed:</b>	22000[RPM]
<b>Noise:</b>	58[dB]
<b>Life Expectancy:</b>	40 degree C 70,000 Hours[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	12[V]
<b>Operating Voltage - Lower:</b>	7[V]
<b>Operating Voltage - Upper:</b>	13.2[V]
<b>Current:</b>	0.63[A]
<b>Input Power:</b>	7.6[W]
<b>Mass:</b>	47[g]
<b>Tach / Locked Rotor Output:</b>	Tach Output
<b>Status:</b>	Active

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[03828DA-12R-AU-00](#)