

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010321041](#)
Status: **Active**
Overview: SPOX Connector System
Description: 5.08mm Pitch SPOX Wire-to-Board Header, Vertical, with Friction Lock, 4 Circuits

Documents:

| | |
|---|---|
| 3D Model | Product Specification PS-5197-003 (PDF) |
| Drawing (PDF) | Product Specification PS-5197-004 (PDF) |
| 3D Model (PDF) | Product Specification PS-5281-002-001 (PDF) |
| Product Specification PS-5197-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|---------------------------------------|
| Product Family | PCB Headers |
| Series | 5281 |
| Application | Power, Wire-to-Board |
| Overview | SPOX Connector System |
| Product Name | SPOX |
| UPC | 800753611474 |

Physical

| | |
|--------------------------------|----------------|
| Breakaway | No |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Flammability | 94V-2 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 1567.500/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 3.60mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Bag |
| Pitch - Mating Interface | 5.08mm |
| Plating min - Mating | 5.080µm |
| Plating min - Termination | 5.080µm |
| Polarized to PCB | No |
| Shrouded | Partial |
| Stackable | No |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface: Style | Through Hole |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5281](#) Series

Mates With

[5197](#) SPOX Crimp Housing

Electrical

Current - Maximum per Contact
Voltage - Maximum

7.0A
250V

Material Info

Engineering Number

5281-04A

Reference - Drawing Numbers

Product Specification

PS-5197-001, PS-5197-003, PS-5197-004,
PS-5281-002-001

Sales Drawing

SD-5281-001-001

This document was generated on 05/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[10-32-1041](#)