

**Product information on this page may be out of date.
For the latest information, please refer to the TDK Product Center.**

Product Name **Clamp Filters**
Series **ZCAT Series**
Part Number **ZCAT2032-0930-BK**

Product Lifecycle Stage Production



Specification

Mounting Method Flag	No	
Body Length(L)	Nom	36 m m
Outside Diameter	Nom	19.5 m m
Inside Diameter	Nom	9 m m
Cable Type	Round/Oval Cable	
Cable Diameter (mm)	9max.	
Impedance	Min	50 Ohm
Frequency of Impedance	Nom	50 M Hz
Operating Temperature Range	Min	-40 Cel
	Max	85 Cel
Storage Temperature Range	Min	-40 Cel
	Max	85 Cel
Weight	Nom	22.7 g

Summary/Applications/Features

Summary	Unique plastic case ensures simple, convenient installation and includes a self-holding mechanism to prevent slippage on cables.
Applications	Personal computers, word processors, monitors, hard disk drives, digital telephones, audio devices, electronic musical instruments, video games, copiers and facsimiles.
Features	Ferrite core provides excellent absorption of high-frequency EMC. Highly effective as countermeasure against common mode EMC without adverse effect on signal quality. Large core size prevents saturation during large signal surges.

Packaging

Packing	Box	
Minimum Package Qty	Nom	420 Pcs
Minimum Order Qty	Nom	420 Pcs

[Details](#)

[Catalog Info.](#)

[Caution]
 Specifications which provide more details for the proper and safe use of the described product are available upon request.

[Notice of Revision and Improve]
 All specifications are subject to change without notice.