




APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	08/01/09	
A		UPDATE DRAWING	4/21/21	LH/RC



NO.	DESCRIPTION	MATERIAL	FINISH
4	COVER TAPE	PI	AMBER
3	CONTACT PIN	PB CU	GOLD
2	INSULATOR	PTFE	WHITE
1	BODY	BRASS	GOLD

Electrical:  
 Frequency range: DC-6 GHz  
 Nominal Impedance: 50 OHM  
 Voltage rating: 335 Volts max  
 Temperature Rating:  
 Operating temperature: -55°C to +155°C  
 Environmental:  
 Lead free, RoHS compliant.

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

**ADAM TECH**

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

DRAWN	SS	08/01/09
CHECKED		
APPROVED		

TITLE MCX JACK, PCB, VERTICAL		
SIZE X	PART NO. RF11-01-T-00-50-G	REV. -
REF: S00277T	SCALE: NTS	SHEET 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH