


Patch cable - NBC-R4AC1/20,0-94G/R4AC1-RD - 1421147

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Patch cable, degree of protection: IP20, cable length: 20 m, number of positions: 8, 10 Gbps, CAT6A, Ethernet



Key Commercial Data

Packing unit	1 pc
GTIN	 4 0 5 5 6 2 6 2 5 4 7 8 4
GTIN	4055626254784
Weight per Piece (excluding packing)	760.000 g
Custom tariff number	85444210
Country of origin	Poland

Technical data


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Patch cable - NBC-R4AC1/20,0-94G/R4AC1-RD - 1421147

Schematic diagram



Connector pin assignment plug RJ45

Classifications

eCl@ss

eCl@ss 10.0.1	27060308
eCl@ss 11.0	27060308
eCl@ss 7.0	27060308
eCl@ss 9.0	27060308

ETIM

ETIM 6.0	EC001262
ETIM 7.0	EC002599

UNSPSC

UNSPSC 18.0	26121604
UNSPSC 19.0	26121604
UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Patch cable - NBC-R4AC1/20,0-94G/R4AC1-RD - 1421147

Approvals

EAC		19060508
-----	---	----------

Accessories

Accessories

Data cable preassembled

Patch cable - NBC-R4OC/0,3-BC5/R4OC - 1227558



Patch cable, degree of protection: IP20, cable length: 0.3 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/0,5-BC5/R4OC - 1227559



Patch cable, degree of protection: IP20, cable length: 0.5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/1,0-BC5/R4OC - 1227560



Patch cable, degree of protection: IP20, cable length: 1 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/1,5-BC5/R4OC - 1227561



Patch cable, degree of protection: IP20, cable length: 1.5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4AC1/20,0-94G/R4AC1-RD - 1421147

Accessories

Patch cable - NBC-R4OC/2,0-BC5/R4OC - 1227562



Patch cable, degree of protection: IP20, cable length: 2 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/3,0-BC5/R4OC - 1227563



Patch cable, degree of protection: IP20, cable length: 3 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/5,0-BC5/R4OC - 1227564



Patch cable, degree of protection: IP20, cable length: 5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/7,5-BC5/R4OC - 1227565



Patch cable, degree of protection: IP20, cable length: 7.5 m, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/0,3-BC6A/R4OC - 1227572



Patch cable, degree of protection: IP20, cable length: 0.3 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4AC1/20,0-94G/R4AC1-RD - 1421147

Accessories

Patch cable - NBC-R4OC/0,5-BC6A/R4OC - 1227573



Patch cable, degree of protection: IP20, cable length: 0.5 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/1,0-BC6A/R4OC - 1227575



Patch cable, degree of protection: IP20, cable length: 1 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/1,5-BC6A/R4OC - 1227578



Patch cable, degree of protection: IP20, cable length: 1.5 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/2,0-BC6A/R4OC - 1227580



Patch cable, degree of protection: IP20, cable length: 2 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/3,0-BC6A/R4OC - 1227581



Patch cable, degree of protection: IP20, cable length: 3 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4AC1/20,0-94G/R4AC1-RD - 1421147

Accessories

Patch cable - NBC-R4OC/5,0-BC6A/R4OC - 1227583



Patch cable, degree of protection: IP20, cable length: 5 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/7,5-BC6A/R4OC - 1227585



Patch cable, degree of protection: IP20, cable length: 7.5 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/10,0-BC6A/R4OC - 1227588



Patch cable, degree of protection: IP20, cable length: 10 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/12,5-BC6A/R4OC - 1227590



Patch cable, degree of protection: IP20, cable length: 12.5 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4OC/15,0-BC6A/R4OC - 1227591



Patch cable, degree of protection: IP20, cable length: 15 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet

Patch cable - NBC-R4AC1/20,0-94G/R4AC1-RD - 1421147

Accessories

Patch cable - NBC-R4OC/20,0-BC6A/R4OC - 1227593



Patch cable, degree of protection: IP20, cable length: 20 m, CAT6_A, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet