


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	51-00019.M	Connector, PPL7, 5C, 0° plug, 7x38 mm, chrome, solder, Ø2.2-5.2 mm wire, molding style	1	
2	30-00918	Wire, 4C BC, 24 AWG, UL20280, 300V, 80C, 4.8 mm braided shield, FT2, TPU	1	
3	24-00206	Overmold, PPL7 strian relief, 10x24 mm	1	TPU
4	Heat shrink	Black	1	covers jacket end
5	Heat shrink	Black	1	covers drain



Wiring Diagram	wire color
1	Red
2	White
3	Black
4	Yellow
5	Drain/Shield

Revision:	Date:	Description:	Prepared:	Notes:	Size:	Part number:
A	3/27/2018	Initial release	Prepared: AG Digitally signed by AG Date: 2018.04.19 14:39:51 -0700 Verified: AW Digitally signed by AW Date: 2018.04.19 13:44:03 -0700 Dimensions are in millimeters. Tolerances: X: ± 0.5 mm XX: ± 0.3 mm XXX: ± 0.05 mm	RoHS compliant Function test: no open, no short circuit, no intermittent Description: Cable, 1830 mm, 5C PPL7 plug 51-00019.M, to stripped tinned, 24 AWG, UL20280 30-00918	A	10-02262
				Scale: 1:1		
				Sheet 1 of 1		