


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	51-00022.M	Connector, PPL7, 6C, 0° plug, 7x38 mm, chrome, solder, Ø2.2-5.2 mm wire, molding style	1	
2	30-00671	Wire, 5C BC, 28 AWG, UL20280, 300V, 80C, 4.5 mm braided shield, FT2, TPU	1	
3	24-00206	Overmold, PPL7 strian relief, 10x24 mm	1	TPU
4	Heat shrink	black	1	covers jacket end
5	Heat shrink	black	1	covers drain



Wiring Diagram	wire color
1	Red
2	White
3	Black
4	Yellow
5	Blue
6	Drain/Shield

Revision:	Date:	Description:	Prepared:	Notes:
A	3/27/2018	Initial release	Prepared: AG Digitally signed by AG Date: 2018.06.19 14:49:24 -0700 Verified: AW Digitally signed by AW Date: 2018.04.19 16:53:07 -0700	RoHS compliant Function test: no open, no short circuit, no intermittent Description: Cable, 1830 mm, 6C 7mm push-pull plug 51-00022.M, to stripped tinned, 28 AWG, UL20280 30-00671
			Size: Part number: A 10-02264	Scale: 1:1
			Sheet 1 of 1	