


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	51-00022.M	Connector, PPL7, 6C, 0° plug, 7x38 mm, chrome, solder, Ø2.2-5.2 mm wire, molding style	2	
2	30-00671	Wire, 5C BC, 28 AWG, UL20280, 300V, 80C, 4.5 mm braided shield, FT2, TPU	1	
3	24-00206	Overmold, PPL7 strian relief, 10x24 mm	2	TPU



50-00022.M	Wiring Diagram wire color	50-00022.M
1	Red	1
2	White	2
3	Black	3
4	Yellow	4
5	Blue	5
6	Drain/Shield	6

Revision:	Date:	Description:	Prepared:	Notes:
A	3/27/2018	Initial release	AG <small>Digitally signed by AG Date: 2018.04.19 16:20:39 -0700</small>	RoHS compliant Function test: no open, no short circuit, no intermittent
			AW <small>Digitally signed by AW Date: 2018.04.19 16:20:39 -0700</small>	Description: Cable, 1830 mm, 6C PPL7 plug 51-00022.M to same, 28 AWG, UL20280 30-00671
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm XX: ± 0.3 mm XXX: ± 0.05 mm	Size: Part number: A 10-02265
				Scale: 1:1

TENSILITY

tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com