


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	51-00023.M	Connector, PPL7, 6C, 0° socket, 7x38 mm, chrome, solder, Ø2.5-5.2 mm wire, molding style	1	
2	30-00671	Wire, 5C BC, 28 AWG, UL20280, 300V, 80C, 4.5 mm braided shield, FT2, TPU	1	
3	24-00206	Overmold, PPL7 strian relief, 10x24 mm	1	TPU
4	Heat shrink	Black	1	covers jacket end
5	Heat shrink	Black	1	covers drain



Wiring Diagram	wire color
1	Red
2	White
3	Black
4	Yellow
5	Blue
6	Drain/ Shield

Revision:	Date:	Description:	Prepared:	Notes:
A	3/27/2018	Initial release	AG Digitally signed by AG Date: 2018.04.19 16:31:56 -0700	RoHS compliant
			AW Digitally signed by AW Date: 2018.04.19 16:37:40 -0700	Function test: no open, no short circuit, no intermittent
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description: Cable, 1830 mm, 6C PPL7 socket 51-00023.M, to stripped tinned, 28 AWG, UL20280 30-00671
				Size: Part number: A 10-02473
				Scale: 1:1