



Original Dual Wire Ferrules

Dual Wire Insulated

Dual Wire Ferrules have larger diameters and special shaped sleeves that accept two conductors of the same or different size. They provide an efficient connection of multiple wires in the same terminal clamp or simplify wire jumpering between terminal clamps. They are color coded with the same convention as the insulated DIN standard ferrules.


To ensure efficient ferrule crimping always select the smallest ferrule diameter that fits the wire and use only professional crimping tools.

- Sleeve: polypropylene
- Tube: tin plated copper



Tested According To:

CSA Std C22.2 No. 65-93
 CSA Std C22.2 No. 188-M1983
 ANSI/UL Std No. 486A
 ANSI/UL Std No. 486C




- Wire Connectors
- Splicing Wire and Cable Connectors
- Wire Connectors and Soldering Lugs for Use with Copper Conductors
- Splicing Wire Connectors

| Wires x AWG | mm ² | Color | Cat. No. | L1 | L2 | Ferrule Dimensions mm | | | | Std. Pack* | |
|-------------|-----------------|--------|----------|------|-----|-----------------------|------|------|-----|------------|---------|
| | | | | | | D1 | S1 | A | B | S2 | |
| 2x20 | 2x0.50 | White | 2794.0 | 14.6 | 8.2 | 1.4 | 0.15 | 5 | 3 | 0.3 | 500/100 |
| 2x18 | 2x0.75 | Gray | 2775.0 | 14.6 | 8.2 | 1.7 | 0.15 | 5.5 | 3 | 0.3 | 500/100 |
| 2x18 | 2x0.75 | Gray | 2795.0 | 16.4 | 10 | 1.7 | 0.15 | 5.5 | 3 | 0.3 | 500/100 |
| 2x18 | 2x1 | Red | 2776.0 | 15.4 | 8.2 | 2 | 0.15 | 5.8 | 3.2 | 0.3 | 500/100 |
| 2x18 | 2x1 | Red | 2796.0 | 25.2 | 18 | 2 | 0.15 | 5.8 | 3.2 | 0.3 | 500/100 |
| 2x16 | 2x1.5 | Black | 2777.0 | 15.8 | 8.2 | 2.2 | 0.15 | 6.5 | 3.6 | 0.3 | 500/100 |
| 2x16 | 2x1.5 | Black | 2797.0 | 19.6 | 12 | 2.2 | 0.15 | 6.5 | 3.6 | 0.3 | 500/100 |
| 2x14 | 2x2.5 | Blue | 2778.0 | 18.5 | 10 | 2.8 | 0.15 | 8 | 4.5 | 0.4 | 500/100 |
| 2x14 | 2x2.5 | Blue | 2798.0 | 20.5 | 12 | 2.8 | 0.15 | 8 | 4.5 | 0.4 | 500/100 |
| 2x12 | 2x4 | Gray | 2799.0 | 22 | 12 | 3.5 | 0.2 | 9 | 5.2 | 0.5 | 100 |
| 2x10 | 2x6 | Yellow | 2800.0 | 23 | 12 | 4.5 | 0.2 | 11.4 | 6.2 | 0.5 | 100 |
| 2x8 | 2x10 | Red | 2801.0 | 24 | 12 | 5.8 | 0.2 | 13.4 | 7.6 | 0.5 | 100 |
| 2X6 | 2x16 | Blue | 2802.0 | 29 | 16 | 8.3 | 0.3 | 17.2 | 9.5 | 0.6 | 50 |

INSULATED FERRULES Assortment Box

Handy Assortment Boxes for convenient dispensing and storage of Industry and DIN Standard Insulated Ferrules. Types AB1-S and AB1-D are equipped with five different ferrule sizes. Types AB2-S and AB2-D are equipped with four different ferrule sizes. Contents of each box is listed.



* Different standard packs are available for many ferrules. To order the desired standard pack, please use the quantity required as a suffix to the Cat. No.

Example: Cat. No. 2794.0/100 for a standard pack of 100



AB1-S



AB2-S

CRIMPER SELECTOR GUIDE
page 18

| Ferrule Qty. | AWG | mm ² | Ferrule Cat. No. | Ferrule Color | Type | Cat. No. | Std. Pack |
|--------------------------------|-----|-----------------|------------------|---------------|--------------|---------------|-----------|
| AB1-S Industry Standard | | | | | AB1-S | 2884.9 | 1 |
| 50 | 20 | 0.5 | 2201.0 | Orange | | | |
| 100 | 20 | 0.75 | 2202.0 | White | | | |
| 100 | 18 | 1 | 2399.0 | Yellow | | | |
| 100 | 16 | 1.5 | 2204.0 | Red | | | |
| 50 | 14 | 2.5 | 2206.0 | Blue | | | |
| AB2-S Industry Standard | | | | | AB2-S | 2885.9 | 1 |
| 50 | 12 | 4 | 2208.0 | Gray | | | |
| 20 | 10 | 6 | 2210.0 | Black | | | |
| 20 | 8 | 10 | 2212.0 | Ivory | | | |
| 10 | 6 | 16 | 2214.0 | Green | | | |
| AB1-D DIN Standard | | | | | AB1-D | 2884.0 | 1 |
| 50 | 20 | 0.5 | 2864.0 | White | | | |
| 100 | 20 | 0.75 | 2867.0 | Gray | | | |
| 100 | 18 | 1 | 2871.0 | Red | | | |
| 100 | 16 | 1.5 | 2841.0 | Black | | | |
| 50 | 14 | 2.5 | 2845.0 | Blue | | | |
| AB2-D DIN Standard | | | | | AB2-D | 2885.0 | 1 |
| 50 | 12 | 4 | 2848.0 | Gray | | | |
| 20 | 10 | 6 | 2851.0 | Yellow | | | |
| 20 | 8 | 10 | 2853.0 | Red | | | |
| 10 | 6 | 16 | 2855.0 | Blue | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[2884.9](#) [2885.9](#)