

Maximum-Minimum Recording Thermometers. A wide choice of designs and ranges for all countries and markets. Packed singly.

1. Heavy-Duty Magnet Max-Min. Moulded in robust grey plastic. Separate resetting magnet.

-30/50C & -20/120F	Product No. 12/039/3
-30/50C	12/039/2
-45/50C & -40/120F	12/939/3

2. Press-Button Max-Min with enclosed case design in green. No separate magnet needed.

-30/50C & -20/120F	Product No. 12/642/3
-30/50C	12/642/2
-45/50C & -40/120F	12/952/3

3. Dial Max-Min Thermometer. Robust hanging 100mm metal case with chrome bezel. Black needle moves blue and red pointers into position. Use central knobs to reset.

-30/60C & -20/140F	Product No. 12/643/3
--------------------	----------------------

RS 206-8929 = 12/642/3

Left. 255mm Special Purpose Thermometers. Robust white mouldings printed with zoned scales, and red spirit tubes.

1. Beer Cellar & Storage Thermometer. This has the scale zoned in red for keg and traditional beers (10/15C). Packed singly.

5/25C & 40/80F	Prod. No. 14/705/3
----------------	--------------------

2. Banana Curing Thermometer. On this model the zones are clearly marked for slow, medium and quick curing as well as showing levels that are too cold or hot. Packed singly.

5/25C & 40/80F	Prod. No. 14/706/3
----------------	--------------------

3. U.K. Factory & Shops Act Thermometer. Zoned scale. Packed singly.

-10/50C & 20/120F	Prod. No. 14/390/3
-------------------	--------------------

RS 206-8907 = 14/390/3

1. Horizontal Freezer Thermometer. Moulded in food-safe white plastic, with red zoned scale. Will hang or stand. Packed singly.

-20/40C nominal	Product No. 22/484/2
-----------------	----------------------

RS 206-8935 = 22/484/2