

Rittal – The System.

Faster – better – everywhere.

► Wall-mounted enclosures EL, 3-part with mounting plate and mounting angles, static installation – EL 2259.605

Date : Apr 27, 2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wall-mounted enclosures EL, 3-part with mounting plate and mounting angles, static installation – EL 2259.605

created: 27.04.2021 build on www.rittal.com/uk-en



Product description

Design:	with mounting plate and mounting angles, static installation
Description:	Wall-mounted enclosure with optimum accessibility due to hinged part.
Material:	Wall and hinged part: Sheet steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish:	Powder-coated
Colour:	Wall and hinged part: RAL 7035 Glazed door: RAL 7035/7015 (slate grey)
Protection category IP to IEC 60 529:	IP 55
IK Code:	IK08
Supply includes:	Wall section with solid gland plate, top and bottom and mounting plate (supplied loose). Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles, front, static installation Designer glazed door 1 double-kit key no. 5 Mini-comfort handle for lock inserts Security lock 3524 E
Basic material:	Sheet steel

Product description

Dimensions:	Width: 600 mm Height: 478 mm Units: 9 U Depth: 473 mm
Depth hinged part:	316 mm
Installation depth:	420 mm
Clearances:	Clearance width: 502 mm Clearance height: 415 mm
Mounting plate:	Width: 485 mm Height: 432 mm
Wall section:	Depth: 135 mm
Load capacity:	Hinged part, static (max.): 450 N
Packs of:	1 pc(s).
Weight/pack:	33 kg
EAN:	4028177324398
Customs tariff number:	94032080
ETIM 7.0:	EC002500
ETIM 6.0:	EC002500
eCl@ss 8.0/8.1:	27180208
eCl@ss 6.0/6.1:	27180208
Product description:	EL Wall-mounted enclosures, 3-part, 9 U, WHD: 600x478x473 mm, Protection category: IP 55, Designer glazed door

Approvals

Approvals:	Germanischer Lloyd Lloyds Register of Shipping UL + C-UL
Certificates:	EAC IK-Code NA Protection category

