


DRAWING FOR REFERENCE
 WE RESERVE THE RIGHT TO MAKE CHANGES TO OUR
 STANDARD PRODUCTS. PLEASE CONSULT WITH BUD INDUSTRIES
 PRIOR TO USING THIS DRAWING FOR DESIGN PURPOSE.


INSIDE VIEW OF BODY
 COVER NOT SHOWN



NOTES:

- 1- MATERIAL: BODY - GRAY POLYCARBONATE RESIN
 10% GLASS FIBER FILLED
 COVER - GRAY POLYCARBONATE OR
 CLEAR (-C SUFFIX) POLY-
 CARBONATE
- 2- UL508 / NEMA TYPE 4X WITH IP-67 TUV RATING
 & UL-94 5VA
- 3- CONTINUOUS Poured NEOPRENE GASKET IN COVER
- 4- SUPPLIED WITH TWO OR FOUR M5 x 8mm LG.
 TRUSS HEAD ZINC PLATED STEEL SCREWS
 (ITEMS NOT SHOWN)
- 5- DIMENSIONS ARE INCH [MM]
- 6- OPTIONAL ACCESSORIES NOT INCLUDED:
 INTERNAL MOUNTING PLATES 16 GA. STEEL OR ABS
 EXTERNAL MOUNTING BRACKETS NBX-10922
 (STAINLESS STEEL) OR PIX-4117 (GRAY POLY-
 CARBONATE RESIN 10% GLASS FIBER FILLED)

BOSS LOCATIONS FOR REFERENCE. QUANTITY AND DISTRIBUTION MAY DIFFER FROM BOX TO BOX



BOXES OF DIFFERENT SIZE IN THIS SERIES WILL NOT HAVE THE SAME SHAPE AND LOOK

PART NO.		DIMENSIONS							LATCH QTY.
		A	B	C	D	E	F	G	
PTH-22706-L	PTH-22706-LC	9.84 [250]	5.91 [150]	5.12 [130]	3.15 [80]	---	---	8.27 [210]	2
PTH-22730-L	PTH-22730-LC	15.75 [400]	11.75 [298]	5.91 [150]	4.72 [120]	12.75 [324]	9.06 [230]	13.25 [336]	2
PTH-22746-L	PTH-22746-LC	14.96 [380]	7.48 [190]	5.04 [128]	3.86 [98]	4.72 [120]	12.20 [310]	---	2
PTH-22758-L	PTH-22758-LC	22.05 [560]	11.02 [280]	5.12 [130]	3.94 [100]	19.31 [490]	8.27 [210]	---	2
PTH-22760-L	PTH-22760-LC	16.93 [430]	13.00 [330]	7.09 [180]	5.91 [150]	14.17 [360]	10.22 [260]	14.75 [375]	2
PTH-22762-L	PTH-22762-LC	22.05 [560]	14.96 [380]	7.09 [180]	5.83 [148]	12.20 [310]	19.29 [490]	---	2
PTH-22780-L	PTH-22780-LC	9.84 [250]	3.15 [80]	3.35 [85]	1.97 [50]	7.87 [200]	1.59 [40]	8.65 [220]	1