

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Cable duct for installation and mounting in control cabinets, light gray, halogen-free, comprising upper part and mounting base, width: 25 mm, height: 60 mm, length: 2000 mm

Your advantages

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Commercial Data

| | |
|--------------------------------------|---------------------|
| Item number | 3240342 |
| Packing unit | 1 pc |
| Minimum order quantity | 15 pc |
| Sales Key | BE74 |
| Product Key | BE7441 |
| Catalog Page | Page 579 (C-3-2019) |
| GTIN | 4046356508278 |
| Weight per Piece (including packing) | 540 g |
| Weight per Piece (excluding packing) | 520 g |
| Customs tariff number | 39259020 |
| Country of origin | DE |

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>




Technical Data

Connection data

| | |
|-----------------------|---------------------|
| Nominal cross section | 836 mm ² |
|-----------------------|---------------------|

Dimensions

| | |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width | 25 mm |
| Height | 60 mm |
| Length | 2000 mm |

Material specifications

| | |
|----------------------------------------|---------------------|
| Color | light grey RAL 7035 |
| Material | PC/ABS |
| Flammability rating according to UL 94 | V0 |
| Components | halogen-free |

Cable/line

| | |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 90 °C |
|---------------------------------|------------------|

CD-HF 25X60 - Cable duct


3240342

<https://www.phoenixcontact.com/us/products/3240342>



Drawings

Dimensional drawing



Base perforation according to DIN EN 50085

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>




Approvals

 **CSA**
Approval ID: 248269

 **UL Recognized**
Approval ID: FILE E 328576

 **VDE Zeichengenehmigung**
Approval ID: 40028972

 **EAC**
Approval ID: RU C-DE.PB68.W.00513

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27400703 |
| ECLASS-12.0 | 27400703 |
| ECLASS-13.0 | 27400703 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC000012 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>



Environmental Product Compliance

| | |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>



Accessories

CD-HF COVER 25 - Cover profile

3240369

<https://www.phoenixcontact.com/us/products/3240369>



Cover for cable duct, light gray, halogen-free, width: 25 mm, length: 2000 mm

RVT-PA 4 - Fastening clip

3240498

<https://www.phoenixcontact.com/us/products/3240498>



Plastic body-bound rivet, for hole diameter of 4 mm and a material thickness of 1.5 ... 6 mm

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>



RVT-PA 6 - Fastening clip

3240499

<https://www.phoenixcontact.com/us/products/3240499>



Plastic body-bound rivet, for hole diameter of 6 mm and a material thickness of 1.5 ... 6 mm

UNIFOX-RVT P 4 - Tool

1212478

<https://www.phoenixcontact.com/us/products/1212478>



Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets

CD-HF 25X60 - Cable duct

3240342

<https://www.phoenixcontact.com/us/products/3240342>



UNIFOX-RVT P 6 - Tool

1212509

<https://www.phoenixcontact.com/us/products/1212509>

Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets



Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com