


Model 4846-UU
SMA Plug to SMA Plug, RG178B/U



Model 4846-UU
SMA Plug to SMA Plug, RG178B/U

Small size, and durability for
confident connections

Features

- DC - 4GHz bandwidth.
- Connectors are precision machined and gold-plated for low loss.
- Perfect for applications where space, weight, performance and ease of connection are required.

Materials

SMA Male Connector:
Center Contact: Brass, Gold Plated
Connector Body: Brass, Gold Plated
Crimp Ferrule: Copper, Nickel Plated
Insulators: PTFE

Specifications

Cable Type	RG178B/U
Impedance	50Ω
Frequency Range	DC - 4GHz
Insulation Resistance	≥ 5000 MΩ
Insulator Withstand	1000V
Temperature Range	-65° C to +165°C (-85°F to +329°F)
Jacket	FEP
Cable O.D.	0.071" (1.8mm)
Center Conductor (mm)	7 x .1 silver coated copper covered steel

Ordering Information

Model: **4846**
Cable Designator: **UU** = RG178B/U
Standard Lengths: **12", 24", 36", 48", 60"**
 - 12" ± .157" (305mm ± 4mm)
 - 24" ± .275" (610mm ± 7mm)
 - 36" ± .394" (914mm ± 10mm)
 - 48" ± .512" (1219mm ± 13mm)
 - 60" ± .630" (1524mm ± 16mm)
 Ordering Example: **4846-UU-48**, Cable is RG178B/U with length of 48" (1219mm)

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500
Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4846-UU-60](#) [4846-UU-24](#) [4846-UU-36](#) [4846-UU-12](#) [4846-UU-48](#)