


Coaxial Cable Connector 25_SMA-50-2-15/111_N

Description

Straight panel cable jack, flange mount

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0027 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00008786
Assembly instruction	DOC-0000179086
Mounting hole	DOU-00008784

Ordering Information

Single package	25_SMA-50-2-15/111_NE
----------------	-----------------------

Additional Information

Suitable cables	EZ_86_TP_M17, SUCOFORM_86, MULTIFLEX_86
-----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[25_SMA-50-2-15/111_NE](#)