

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFPart-Ty Relea ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'PRT2S-M4'

Your search criteria matched only one product, shown below

PRT2S-M4Y



- For indoor use
- Extended release tab permits easy release and re-use where changes are anticipated during development, production or servicing in the field
- To release, grasp the head of the cable tie, deflect release tab, and pull the cable tie away from the bundle
- One-piece construction for consistent performance and reliability
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

Part Number	PRT2SM4Y
RoHS Compliancy Status	Compliant
Note	PRT2SM4Y replaces PRT2SM4
Part Description	Cable Tie, Releasable, 7.4", Standard cross section
Product Type	Cable Ties
Material	Nylon 6.6
Color	Yellow
CSA Certified	Yes
UL Listed (File #E56854)	Yes
UL Recognized (File #E56854)	Yes
Length (In.)	7.4
Length (mm)	188
Width (In.)	.190
Width (mm)	4.8
CE Compliant	Yes
Cross Section	Standard
Head Height (In.)	.219
Head Height (mm)	5.6
Head Width (In.)	.316
Head Width (mm)	8.0
Locking Style	Releasable
Material Flammability Rating	UL 94V-2
Max. Bundle Diameter (In.)	1.88
Max. Bundle Diameter (mm)	48
Max. Continuous Use Temperature	185°F (85°C)
Min. Loop Tensile Strength (Lbs.)	50
Min. Loop Tensile Strength (N)	222
Pricing Description	Cable Tie, Releasable, 7.4"L (188mm), Standard, Nylon, Yellow
Thickness (In.)	.052
Thickness (mm)	1.3
Tool	Hand install only
Min. Order UOM	PC
Min. Order Qty.	1000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.