



Jigsawing and **Sabre Sawing**

[Back](#)

Grey – for wood

The product name describes the characteristics	The features	The blade quality
basic for Wood	Good and cost-effective	HCS, milled
speed for Wood	For fast cuts	HCS, ground
clean for Wood	Fine and clean cuts	HCS, ground
extra-clean for Wood	Tear-free cuts in wood	HCS, ground
precision for Wood	Exact cut at accurate angles	HCS, ground
PROGRESSOR for Wood	Fast through thick and thin	HCS, ground
speed for HardWood	For quick cuts, also in hardwood	BIM, ground
clean for HardWood	For fine cuts, also in hardwood	BIM, ground
extra-clean for HardWood	Tear-free in wood, also in hardwood	BIM, ground
special for Laminate	For precise, clean cuts in laminate	BIM, ground



Blue – for metal

The product name describes the characteristics	The features	The blade quality
basic for Metal	Good and cost-effective	HSS, milled
basic for Inox	Good and cost-effective for stainless steel	BIM, milled
flexible for Metal	Breakproof, long lifetime	BIM, milled
flexible for Metal-Sandwich	Break proof, long lifetime	BIM, milled
speed for Metal	Fast, breakproof, long lifetime	BIM, milled
PROGRESSOR for Metal	Fast through thick and thin	HSS, milled
special for Alu	Ideal for aluminium, soft and non-ferrous metal	HSS, milled



White – for wood and metal

The product name describes the characteristics	The features	The blade quality
PROGRESSOR for Wood & Metal	Universal, fast through thick and thin	BIM, milled



Black – for special applications

The product name describes the characteristics	The features	The blade quality
special for Inox	For stainless steel	TC, ground
special for Synthetics	For abrasive synthetics	TC, ground
special for Fiber & Plaster	For fibre and cement materials	TC, ground
special for Ceramics	For ceramic materials	TC, grit
special for Acrylic	Clean through acrylic glass	HSS, ground
special for Soft-Material	Cuts soft materials	HCS, ground



Quality controlled

for optimum results

HCS

- ▶ Carbon steel for use with softer materials such as softwood, wood fibreboards and soft plastics

BIM

- ▶ Bi-metal, a highly elastic bond of HSS and HCS to meet the greatest demands. Especially suitable for use in hardwood, abrasive wooden materials, hard plastics, and harder materials such as non-ferrous metal and ferrous metal
- ▶ The flexible BIM saw blades are used, for example, if there is a risk of shank breakage
- ▶ They have a lifetime about twice as long as the HSS blades and last approx. 10 times longer than HCS blades. This means that they are excellent value for money

HSS


- ▶ Fully hardened high-grade high speed steel for use with harder materials such as metal, aluminium and non-ferrous metal

TC

- ▶ Tungsten carbide saw blades are particularly powerful
- ▶ The tungsten carbide teeth bite through glass fibre reinforced plastic, cement-bonded fibreboards or plasterboard
- ▶ Tungsten carbide tooth strips cut stainless steel
- ▶ A coating with tungsten carbide grit (= RIFF) cuts through abrasive materials such as wall tiles or glass fibre reinforced plastic

The right geometry

is what's important



Milled and side set teeth

Blade with relatively rough cut and quick work progress cutting into hard and softwood, aluminium, plastics and non-ferrous metals (e.g. T 111 C, T 345 XF).

Milled and wavy set teeth

Blade for fine, straight cutting results into plywood, soft steel, aluminium, non-ferrous metals and plastics (e.g. T 119 B, T 118 A).

Ground and side set teeth

Blade for quick cuts in wood (e.g. T 144 D, T 244 D).

Ground and taper ground teeth

Blade with taper ground spine for fine and clean cuts in wood and plastic (e.g. T 101 B, T 234 X).

Speed for Metal jigsaw blades

Unrivalled cutting speed and superior longevity in metal










The significance of steel as the most important building material is constantly increasing. Metal components have to be cut to length or adjusted in size, in order to meet given size or space requirements on the construction site.





Conventional metal jigsaw blades are often unsatisfactory where cutting speed and lifetime are concerned, and therefore do not meet the expectations of professional users. The new jigsaw blades in the Speed for Metal series offer unrivalled cutting speed and superior lifetime when cutting metal, e.g. sawing thick perforated sheet metals or thick-walled metal profiles.

We have achieved unsurpassed sawing performance with a metal-optimised material selection and tool design:

- ▶ 50% higher cutting speed
- ▶ Three times the lifetime of conventional jigsaw blades made of HSS steel



	T 121 GF For very thin sheet metals	
	T 121 AF For thin sheet metals and perforated sheet metals	
	T 121 BF For medium-thick sheet metals and perforated sheet metals	

	T 321 AF For thin-walled metal pipes and profiles	
	T 321 BF For thick-walled metal pipes and profiles	

Powerful saw blades

make work noticeably easier



Ideal for precise, clean cuts on both sides in laminate and plastic-coated boards.



With the Speed for Wood T 244 D, curves are no problem – even in wood core plywood.




With the Precision for Wood T 144 DP, you can cut kitchen worktops and doors with precise angular accuracy.



The Basic for Inox jigsaw blade T 118 GFS is particularly suitable for working in thin stainless steel sheets.



Using the Progressor for Wood and Metal T 345 XF at the construction site, you can cut through not only wood with nails without a problem, but also sheet metals, pipes and aluminium profiles.



Extraclean for Wood.


Particularly fine, clean, tear-free cuts on both sides in wood

An absolute first: tear-free, straight cuts on both sides in wood; regardless of whether the jigsaw is guided from above or below. The wood no longer has to be marked from underneath, making incorrect marking a thing of the past. For clean and accurate working with high cutting speed and long lifetime.

The teeth make it all possible: the tooth strip with its revolutionary tooth geometry* results in this exceptional work.

* patent pending

The right jigsaw blade for any requirement



Ideal for adjusting shelves made of softwood


















Accurate cutting of visible end strips



















The T 308 BF is perfectly suitable for working in high-quality panel materials laminated on both sides (HPL layer thickness min. 0.7 mm).

The right saw blade for every application




































Wood

Material to be processed	Dimensions max. mm	Subbrand	Type of cut							
			 Straight, fine	 Straight, coarse	 Curve, fine	 Curve, coarse	 At accurate angles	 Thin and thick		
 Softwood, wood core plywood	1.5 – 15	clean Wood						T 101 AO		
	2 – 15	basic Wood		T 119 B				T 119 BO		
	3 – 65	PROGRESSOR Wood		T 234 X						T 234 X
		precision Wood		T 301 BCP					T 301 BCP	
	3 – 30	clean Wood		T 101 B						
		clean Wood		T 101 BR						
	4 – 50	basic Wood			T 111 C					
	5 – 50	speed Wood			T 144 D				T 244 D	
		extra-clean Wood		T 308 B					T 308 BO	
		precision Wood			T 144 DP				T 144 DP	
	5 – 100	speed Wood			T 344 D					
		precision Wood			T 344 DP				T 344 DP	
	10 – 45	clean Wood		T 101 D						
10 – 65	clean Wood		T 301 CD							
 Hardwood, MDF, chipboard	3 – 30	clean HardWood		T 101 BF						
		clean HardWood		T 101 BRF						
	4 – 65	clean HardWood		T 301 CDF						
	5 – 50	speed HardWood			T 144 DF					
		extra-clean HardWood		T 308 BF					T 308 BOF	
5 – 100	speed HardWood			T 344 DF						
 Plywood	1.5 – 15	clean Wood						T 101 AO		
	2 – 15	basic Wood		T 119 B				T 119 BO		
	3 – 30	clean Wood		T 101 B						
	5 – 50	extra-clean Wood		T 308 B				T 308 BOF		
 Construction wood	<30	clean Wood		T 101 B						
	<65	PROGRESSOR Wood		T 234 X					T 234 X	
	<100	speed Wood			T 344 D					
		speed HardWood			T 344 DF					
		precision Wood			T 344 DP				T 344 DP	
<135	speed Wood			T 744 D						
 Laminated panels	1.5 – 15	clean HardWood						T 101 AOF		
	2 – 30	clean HardWood		T 101 AIF						
	3 – 30	clean HardWood		T 101 BRF						
	5 – 50	speed HardWood			T 144 DF					
		extra-clean HardWood		T 308 BF					T 308 BOF	
	5 – 100	speed HardWood			T 344 DF					
 Kitchen tops/ Worktops	<45	clean HardWood		T 101 BRF						
	<50	extra-clean HardWood		T 308 BF				T 308 BOF		
	<50	precision Wood			T 144 DP				T 144 DP	
		precision Wood		T301BCP					T 301 BCP	
 Laminates	1.5 – 15	special Laminate		T 101 BIF				T 101 AOF		
 Plastics	<30	clean Wood		T 101 B						
		clean HardWood		T 101 AIF						
		clean HardWood		T 101 BF						
 Glass fibre reinforced plastic/ epoxy	<30	clean HardWood		T 101 AIF						
		clean HardWood		T 101 BF						













Wood and metal

Material to be processed	Dimensions max. mm	Subbrand	Type of cut						
									
 Construction timber with nails	<65	PROGRESSOR 		T 345 XF					T 345 XF
 Construction wood	<65	PROGRESSOR 		T 345 XF					T 345 XF
 Pipes, profiles, thick-walled (open and closed)	<65	PROGRESSOR 		T 345 XF					T 345 XF
 Aluminium	<65	PROGRESSOR 		T 345 XF					T 345 XF
 Glass fibre reinforced plastic/epoxy	<65	PROGRESSOR 		T 345 XF					T 345 XF










Metal

Material to be processed	Dimensions max. mm	Subbrand	Type of cut							
										
 Sheet metals	0.5 – 1.5	basic 	T 118 G							
		speed 	T 121 GF							
	1 – 3	basic 	T 118 A		T 218 A					
		speed 	T 121 AF							
		basic 	T 318 A							
	2.5 – 6	basic 	T 118 B							
		speed 	T 121 BF							
		basic 	T 318 B							
	1.5 – 10	PROGRESSOR 	T 123 XF						T 123 XF	
	3 – 15	special 	T 127 D		T 227 D					
 Perforated sheet metals	0.5 – 1.5	speed 	T 121 GF							
		1 – 3	flexible 	T 118 AF						
	speed 		T 121 AF							
	flexible 		T 318 AF							
	1.5 – 4	flexible 			T 118 EOF					
	2.5 – 6	flexible 	T 118 BF							
		speed 	T 121 BF							
		flexible 	T 318 BF							
	 Aluminium, non-ferrous metal	<30	special 	T 127 D		T 227 D				
			PROGRESSOR 	T 123 XF						T 123 XF
<65		basic 	T 318 A							
		basic 	T 318 B							
		flexible 	T 318 AF							
		flexible 	T 318 BF							
		speed 	T 321 AF							
		speed 	T 321 BF							


























Metal

Material to be processed	Dimensions max. mm	Subbrand	Type of cut						
									
 Pipes, profiles (closed)	<30	PROGRESSOR Metal	T 123 XF						T 123 XF
	<65	basic Metal	T 318 A						
		basic Metal	T 318 B						
		flexible Metal	T 318 AF						
		flexible Metal	T 318 BF						
		speed Metal	T 321 AF						
		speed Metal	T 321 BF						
	 Profiles (open)	<65	flexible Metal	T 318 AF					
flexible Metal			T 318 BF						
flexible Metal			T 318 BF						
speed Metal			T 321 AF						
 Inox sheets	0.5 – 1.5	basic inox	T 118 GFS						
	1.5 – 4	basic inox	T 118 EFS						
 Sandwich material	<65	flexible Metal	T 318 AF						
		flexible Metal	T 318 BF						
		speed Metal	T 321 AF						
 Plastics	<30	special Alu	T 127 D			T 227 D			
	<65	flexible Metal	T 318 AF						
flexible Metal		T 318 BF							
 Glass fibre reinforced plastic/epoxy	<30	special Alu	T 127 D			T 227 D			
	<65	flexible Metal	T 318 AF						
		flexible Metal	T 318 BF						
		speed Metal	T 321 AF						
		speed Metal	T 321 BF						

Special applications

Material to be processed	Dimensions max. mm	Subbrand	Type of cut						
									
 Inox sheets	1.5 – 3	special inox	T 118 AHM						
	2 – 5	special inox	T 118 EHM						
 Glass fibre reinforced plastic/epoxy	<50	special FiberPlaster				T 141 HM			
	<65	special Synthetics	T 301 CHM						
	<80	special FiberPlaster				T 341 HM			
 Plasterboard	5 – 50	special FiberPlaster				T 141 HM			
	5 – 80	special FiberPlaster				T 341 HM			

Special applications

Material to be processed	Dimensions max. mm	Subbrand	Type of cut					
			 Straight, fine	 Straight, coarse	 Curve, fine	 Curve, coarse	 At accurate angles	 Thin and thick
 Porous concrete	<80	special  FiberPlaster		T 341 HM				
 Fibre cement	5 – 50	special  FiberPlaster		T 141 HM				
	5 – 80	special  FiberPlaster		T 341 HM				
 Ceramic wall tiles	5 – 10	special  Ceramics	T 150 RIFF					
	5 – 15	special  Ceramics	T 130 RIFF					
 Perspex	2 – 20	special  Acrylic	T 101 A					
 Polystyrene	<50	special  Soft-Material	T 113 A					
	<100	special  Soft-Material	T 313 AW					
 Cardboard, carpet, leather	<50	special  Soft-Material	T 113 A					
	<100	special  Soft-Material	T 313 AW					
 Rubber	<50	special  Soft-Material	T 113 A					
	<100	special  Soft-Material	T 313 AW					



Jigsaw blades for wood




Single lug shank

Jigsaw blades – Basic for Wood

Good and cost-effective

basic for Wood

Softwood, panels [mm]	Plywood [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3163140...	Discount group	List Price ex vat
Product properties				Ordering information						




T 119 B



HCS, wavy set, milled
Softwood (2-15 mm), plywood, chipboards, wood core plywood, fibre boards

2-15	2-15	92	1.9-2.3	2 608 630 878	C1b	3	10	007245	GAJ	3.22
				2 608 630 037	C1b	5	10	006835	GAJ	5.06




T 119 BO



HCS, wavy set, milled
Softwood (2-15 mm), plywood, chipboard, wood core plywood, fibre boards, especially for curve cuts

2-15	2-15	83	2	2 608 637 788	C1b	3	10	045940	GAJ	4.11
				2 608 630 310	C1b	5	10	006941	GAJ	6.45
				2 608 637 879	C1a	100	1	067461	GAJ	109.74



T 111 C



HCS, side set, milled
Softwood (4-50 mm), chipboard, wood core plywood, fibre boards, quick cut


4-50	-	100	3	2 608 630 808	C1b	3	10	007139	GAJ	2.97
				2 608 630 033	C1b	5	10	006811	GAJ	4.42
				2 608 633 A38	P1a	25	1	264211	GAJ	19.90
				2 608 637 878	C1a	100	1	067454	GAJ	75.14

Jigsaw blades – Speed for Wood

Fast cut



Softwood, panels [mm]	Coarse wood [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information						




T 144 D



HCS, side set, ground
Softwood (5-50 mm), chipboards, wood core plywood, fibre boards

5-50	-	100	4-5.2	2 608 630 560	C1b	3	10	006989	GAJ	4.24
				2 608 630 040	C1b	5	10	006842	GAJ	6.86
				2 608 633 625	P1a	25	1	127691	GAJ	30.87
				2 608 637 880	C1a	100	1	067478	GAJ	116.59




T 244 D



HCS, side set, ground
Softwood (5-50 mm), chipboards, wood core plywood, fibre boards, especially for curve cuts

5-50	-	100	4-5.2	2 608 630 879	C1b	3	10	007221	GAJ	5.78
				2 608 630 058	C1b	5	10	006859	GAJ	8.90
				2 608 633 626	P1a	25	1	127707	GAJ	40.07
				2 608 637 881	C1a	100	1	067485	GAJ	151.37




T 344 D



HCS, side set, ground
Thick construction timber, softwood (5-100 mm), chipboards, wood core plywood, fibre boards

5-100	<100	152	4	2 608 637 944	C1b	3	1	070942	GAJ	13.10
				2 608 633 A34	C1b	5	1	264174	GAJ	18.99



T 744 D



HCS, side set, ground
Softwood/boards, thick construction timber, sandwich materials


5-135	-	180	4	2 608 663 314	C1c	3	1	348591	GAJ	31.91
-------	---	-----	---	---------------	-----	---	---	--------	-----	-------

Jigsaw blades – Clean for Wood

Clean cut



Softwood, panels [mm]	Plywood [mm]	Laminated panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information						




T 101 AO



HCS, pointed teeth, ground teeth and taper ground
Softwood, plywood, laminated panels (1.5-15 mm), especially for curve cuts

1.5-15	1.5-15	1.5-15	83	1.4	2 608 630 559	C1b	3	10	006972	GAJ	5.14
					2 608 630 031	C1b	5	10	006798	GAJ	8.08



T 101 B



HCS, ground teeth and taper ground
Softwood, chipboard, wood core plywood, fibre boards (3-30 mm), plastics/epoxy (dia. <30 mm)

3-30	-	-	100	2.7	2 608 630 557	C1b	3	10	006958	GAJ	5.51
					2 608 630 030	C1b	5	10	006781	GAJ	8.82
					2 608 633 622	P1a	25	1	127660	GAJ	39.69
					2 608 637 876	C1a	100	1	067430	GAJ	149.93



T 101 BR



HCS, ground teeth and taper ground
Softwood, chipboard, wood core plywood, fibre boards (3-30 mm), laminated panels, clean surface

3-30	-	3-30	100	2.5	2 608 633 779	C1b	3	10	091374	GAJ	6.11
					2 608 630 014	C1b	5	10	012454	GAJ	9.70
					2 608 633 623	P1a	25	1	127677	GAJ	43.65




T 101 D



HCS, ground teeth and taper ground
Softwood, chipboards, wood core plywood, fibre boards (10-45 mm)

10-45	-	-	100	4-5.2	2 608 630 558	C1b	3	10	006965	GAJ	5.51
					2 608 630 032	C1b	5	10	006804	GAJ	8.82
					2 608 633 577	P1a	25	1	148726	GAJ	39.69
					2 608 637 877	C1a	100	1	067447	GAJ	149.93



T 301 CD



HCS, ground teeth and taper ground
Softwood, chipboards, wood core plywood, fibre boards (10-65 mm)

10-65	-	-	117	3.0	2 608 637 591	C1b	3	1	016315	GAJ	9.37
					2 608 637 590	C1b	5	1	016308	GAJ	15.81

Extraclean for Wood

Particularly fine, clean, tear-free cuts on both sides in wood

Optimum cutting action due to integrated pre-cutting function.
 No need for time-consuming reworking of the material.
 Fatigue-free working: the jigsaw no longer has to be guided from underneath.



Jigsaw blades – Extraclean for Wood

For tear-free cutting

extra-clean for Wood

Softwood, panels [mm]	Plywood [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 31 651 40...	Discount group	List Price ex vat
Product properties				Ordering information						



T 308 B



HCS, ground teeth and taper ground for softwood and non-abrasive wooden materials

5-50	5-50	117	2.2 XC	2 608 663 750	C1b	3	10	470278	GAJ	7.29
				2 608 663 751	C1b	5	10	470285	GAJ	11.47
				2 608 663 752	P1a	25	1	470292	GAJ	49.68
				2 608 663 753	C1a	100	1	470308	GAJ	187.68



T 308 BO



HCS, ground teeth and taper ground for softwood and non-abrasive wooden materials, especially for curve cuts


5-50	5-50	117	2.2 XC	2 608 663 867	C1b	3	1	535779	GAJ	7.29
				2 608 663 868	C1b	5	1	535786	GAJ	11.47
				2 608 663 869	P1a	25	1	535793	GAJ	49.68

Jigsaw blades – Precision for Wood

Cutting at accurate angles



Softwood, panels [mm]	Coarse wood [mm]	Kitchen worktops [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information							




T 144 DP



HCS, side set, ground
Softwood, chipboards, wood core plywood, fibre boards (5-50 mm), doors, kitchen worktops (<50 mm)

5-50	-	<50	100	4.0	2 608 633 A31	C1b	3	10	244143	GAJ	5.78
					2 608 633 A35	C1b	5	10	264181	GAJ	9.13
					2 608 633 A39	P1a	25	1	264228	GAJ	41.08
					2 608 633 A42	C1a	100	1	264259	GAJ	155.15




T 344 DP



HCS, side set, ground
Thick construction timber, softwood (5-100 mm), chipboards, wood core plywood, fibre boards

5-100	<100	-	152	4.0	2 608 633 A36	C1b	5	1	264198	GAJ	18.27
-------	------	---	-----	-----	----------------------	-----	---	---	--------	-----	-------



T 301 BCP



HCS, ground teeth and taper ground
Softwood, chipboards, wood core plywood, fibre boards (3-65 mm), doors, kitchen worktops (<50 mm)


3-65	-	<50	117	2.5	2 608 633 A37	C1b	5	1	264204	GAJ	13.09
					2 608 633 A40	P1a	25	1	264235	GAJ	58.91

Jigsaw blades – Progressor for Wood

Fast, clean through thick and thin



Softwood, panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
Product properties		Ordering information								




T 234 X



HCS, ground teeth and taper ground
Softwood (3-65 mm), chipboards, wood core plywood, fibre boards

3-65	117	2-3	2 608 633 523	C1b	3	10	169493	GAJ	9.11
			2 608 633 528	C1b	5	10	169509	GAJ	13.03
			2 608 633 524	P1a	25	1	169516	GAJ	58.63
			2 608 633 A41	C1a	100	1	264242	GAJ	221.51

Jigsaw blades for hardwood




Single lug shank

Jigsaw blades – Speed for Hard Wood

Fast cut

speed for **HardWood**

Hardwood, panels [mm]	Coarse wood [mm]	Laminated panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information						




T 144 DF



BIM, side set, ground
Hardwood and softwood (5-50 mm), all types of panels, including laminates

5-50	-	5-50	100	4-5.2	2 608 634 567	C1b	5	10	009430	GAJ	12.87
					2 608 634 990	P1a	25	1	127738	GAJ	57.91



T 344 DF



BIM, side set, ground
Thick hardwood and softwood (5-100 mm), all types of panels, including laminates


5-100	<100	5-100	152	4	2 608 634 243	C1b	5	1	091947	GAJ	28.00
-------	------	-------	-----	---	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Clean for Hard Wood

Clean cut

clean for **HardWood**

Hardwood, panels [mm]	Laminates [mm]	Kitchen worktops [mm]	Glass fibre reinforced plastic/epoxy [mm]	Laminated panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information								




T 101 AOF



BIM, pointed teeth, ground teeth and taper ground
Hardwood, laminated panels/HPL (1.5-15 mm), plywood, especially for curve cuts, no tears

1.5-15	1.5-15	-	-	1.5-15	83	1.4	2 608 634 233	C1b	5	10	091848	GAJ	16.17
--------	--------	---	---	--------	----	-----	----------------------	-----	---	----	--------	-----	-------



T 101 AIF



BIM, pointed teeth, ground teeth and taper ground
Hardwood, laminated panels/HPL (2-30 mm), glass fibre reinforced plastic/epoxy (dia. <30 mm), no tears


2-30	2-30	-	<30	2-30	100	1.7	2 608 634 897	C1b	5	1	096355	GAJ	16.65
------	------	---	-----	------	-----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Clean for Hard Wood

Clean cut

clean for HardWood

Hardwood, panels [mm]	Laminates [mm]	Kitchen worktops [mm]	Glass fibre reinforced plastic/epoxy [mm]	Laminated panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties							Ordering information						



T 101 BF



BIM, ground teeth and taper ground
 Hardwood, laminated panels/HPL (3-30 mm), glass fibre reinforced plastic/epoxy (dia. <30 mm)

3-30	-	-	<30	3-30	100	2.7	2 608 634 234	C1b	5	10	091855	GAJ	16.65
							2 608 634 988	P1a	25	1	127714	GAJ	76.00




T 101 BRF



BIM, ground teeth and taper ground
 Laminated panels (3-30 mm), kitchen worktops (<45 mm), clean surface

-	3-30	<45	-	3-30	100	2.5	2 608 634 235	C1b	5	10	091862	GAJ	18.10
							2 608 634 989	P1a	25	1	127721	GAJ	81.47



T 301 CDF



BIM, ground teeth and taper ground
 Hardwood and softwood (4-65 mm), laminated panels/HPL


4-65	-	-	-	4-65	117	3.0	2 608 636 229	C1b	5	1	264389	GAJ	20.84
------	---	---	---	------	-----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Extraclean for Hard Wood


For tear-free cutting

extra-clean for HardWood

Plywood [mm]	Kitchen worktops [mm]	Softwood, panels [mm]	Hardwood, panels [mm]	Laminated panels [mm]	Multiplex panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties							Ordering information							



T 308 BF



BIM, ground teeth and taper ground
 for hardwood and abrasive wooden materials



5-50	<50	5-50	5-50	5-50	5-50	117	2.2	2 608 636 568	C1b	3	10	470315	GAJ	12.74
							XC	2 608 636 569	C1b	5	10	470322	GAJ	19.98
								2 608 636 570	P1a	25	1	470339	GAJ	86.75
								2 608 636 571	C1a	100	1	470346	GAJ	327.74

Jigsaw blades – Extraclean for Hard Wood

For tear-free cutting

extra-clean for **HardWood**

Plywood [mm]	Kitchen worktops [mm]	Softwood, panels [mm]	Hardwood, panels [mm]	Laminated panels [mm]	Multiplex panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties							Ordering information							



T 308 BOF



BIM, ground teeth and taper ground for hardwood and abrasive wooden materials, especially for curve cuts

5-50	<50	5-50	5-50	5-50	5-50	117	2.2 XC	2 608 636 639	C1b	3	1	535809	GAJ	12.74
								2 608 636 640	C1b	5	1	535816	GAJ	19.98
								2 608 636 641	P1a	25	1	535823	GAJ	86.75

Jigsaw blades – Special for Laminate

Precise, clean cuts on both sides

special for **Laminate**

Laminates [mm]	Laminated panels [mm]	Multiplex panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information							




T 101 BIF



BIM, ground teeth and taper ground Laminates (1.5-15 mm), laminated panels/HPL (1.5-15 mm), multiplex panels (1.5-15 mm)

1.5-15	1.5-15	1.5-15	83	1.7	2 608 636 431	C1b	5	10	393416	GAJ	16.66
--------	--------	--------	----	-----	----------------------	-----	---	----	--------	-----	-------



T 101 AOF



BIM, ground teeth and taper ground Laminates (1.5-15 mm), laminated panels/HPL (1.5-15 mm), multiplex panels (1.5-15 mm)

1.5-15	1.5-15	1.5-15	83	1.4	2 608 636 432	C1b	3	10	393423	GAJ	13.84
--------	--------	--------	----	-----	----------------------	-----	---	----	--------	-----	-------

Jigsaw blades

for wood and metal




Single lug shank

Jigsaw blades – Progressor for Wood and Metal

Universal, fast through thick and thin

PROGRESSOR													
Construction timber with nails [mm]	Coarse wood [mm]	Glass fibre, reinforced plastic/epoxy [mm]	Sheet metals, pipes, profiles [mm]	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties						Ordering information							




T 345 XF



BIM, side set, milled
 Construction timber with nails (<65 mm), wooden materials, plastics, sheet metals, pipes/profiles, inc. aluminium (dia. 3-10 mm)

<65	<65	3-10	3-10	3-10	132	2.4-5	2 608 634 993	C1b	3	10	128018	GAJ	9.77
							2 608 634 994	C1b	5	10	128025	GAJ	15.63
							2 608 634 995	P1a	25	1	128032	GAJ	70.31
							2 608 634 486	C1a	100	1	266208	GAJ	265.71

Jigsaw blades for metal



Single lug shank


Jigsaw blades – Basic for Metal

Good and cost-effective

basic for Metal



Product properties Ordering information




T 118 G



HSS, wavy set, milled
Very thin sheet metals (0.5-1.5 mm)

0.5-1.5	-	-	92	0.7	2 608 631 674	C1b	3	10	007566	GAJ	5.78
					2 608 631 012	C1b	5	10	007283	GAJ	8.50




T 118 A



HSS, wavy set, milled
Thin sheet metals (1-3 mm)

1-3	-	-	92	1.1-1.5	2 608 631 507	C1b	3	10	007399	GAJ	5.51
					2 608 631 013	C1b	5	10	007290	GAJ	8.50
					2 608 638 470	P1a	25	1	127769	GAJ	38.21
					2 608 631 964	C1a	100	1	067492	GAJ	144.34




T 218 A




HSS, wavy set, milled
Thin sheet metals (1-3 mm), especially for curve cuts

1-3	-	-	92	1.1-1.5	2 608 631 672	C1b	3	10	007542	GAJ	6.51
					2 608 631 032	C1b	5	10	007337	GAJ	10.37
					2 608 631 706	C1a	100	1	279482	GAJ	176.24




T 318 A



HSS, wavy set, milled
Thin sheet metals (1-3 mm), pipes + profiles, inc. aluminium (dia. <65 mm)

1-3	<65	<65	132	1.2	2 608 631 319	C1b	5	1	007375	GAJ	19.24
					2 608 631 808	C1a	100	1	279499	GAJ	327.06



T 118 B



HSS, wavy set, milled
Medium-thick sheet metals (2.5-6 mm)


2.5-6	-	-	92	1.9-2.3	2 608 631 673	C1b	3	10	007559	GAJ	5.78
					2 608 631 014	C1b	5	10	007306	GAJ	8.50
					2 608 638 471	P1a	25	1	127776	GAJ	38.21
					2 608 631 965	C1a	100	1	067508	GAJ	144.34

Jigsaw blades – Basic for Metal

Good and cost-effective

basic for Metal

Sheet metals [mm]	Pipes, profiles: closed [mm]	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information						



T 318 B



HSS, wavy set, milled
 Medium-thick sheet metals (2.5-6 mm), pipes + profiles, inc. aluminium (dia. <65 mm), precise angle cut


2.5-6	<65	<65	132	2.0	2 608 631 404	C1b	5	1	007382	GAJ	19.24
-------	-----	-----	-----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Flexible for Metal

Break proof and durable

flexible for Metal

Sheet metals [mm]	Pipes, profiles: closed [mm]	Pipes, profiles: open [mm]	Aluminium [mm]	Sandwich materials [mm]	Glass fibre reinforced plastic/epoxy [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties							Ordering information							




T 118 AF




BIM, wavy set, milled
 Thin sheet metals, perforated sheet metals (1-3 mm)

1-3	-	-	-	-	-	92	1.1-1.5	2 608 634 694	C1b	3	10	035309	GAJ	7.27
								2 608 634 505	C1b	5	10	007627	GAJ	11.25
								2 608 634 991	P1a	25	1	127745	GAJ	50.62




T 318 AF



BIM, wavy set, milled
 Thin sheet metals, perforated sheet metals (1-3 mm), sandwich materials (<65 mm), pipes + open profiles, including aluminium (dia. <65 mm), glass fibre reinforced plastic/epoxy (<65 mm)

1-3	<65	<65	<65	<65	<65	132	1.1	2 608 634 241	C1b	5	1	091923	GAJ	23.43
-----	-----	-----	-----	-----	-----	-----	-----	----------------------	-----	---	---	--------	-----	-------



T 118 EOF



BIM, wavy set, milled
 Thin sheet metals, perforated sheet metals (1.5-4 mm), especially for curve cuts

1.5-4	-	-	-	-	-	83	1.5	2 608 634 237	C1b	5	1	091893	GAJ	12.37
-------	---	---	---	---	---	----	-----	----------------------	-----	---	---	--------	-----	-------



Jigsaw blades – Flexible for Metal

Break proof and durable

flexible for Metal

Sheet metals [mm]	Pipes, profiles: closed [mm]	Pipes, profiles: open [mm]	Aluminium [mm]	Sandwich materials [mm]	Glass fibre reinforced plastic/epoxy [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties							Ordering information							



T 118 BF



BIM, wavy set, milled
Medium-thick sheet metals, perforated sheet metals (2.5-6 mm)



2.5-6	-	-	-	-	-	92	1.9-2.3	2 608 634 503	C1b	5	10	007603	GAJ	11.25
								2 608 634 992	P1a	25	1	127752	GAJ	50.62



T 318 BF




BIM, side set, milled
Medium-thick sheet metals, perforated sheet metals (2.5-6 mm), sandwich materials (<65 mm), pipes + profiles, including aluminium (dia. <65 mm), glass fibre reinforced plastic/epoxy (<65 mm)



2.5-6	<65	<65	<65	<65	<65	132	1.8	2 608 634 242	C1b	5	1	091930	GAJ	23.43
-------	-----	-----	-----	-----	-----	-----	-----	----------------------	-----	---	---	--------	-----	-------

Speed for Metal

Unrivalled cutting speed and superior lifetime in metal




Jigsaw blades – Speed for Metal

Fast, break proof and durable

speed **for Metal**

Sheet metals [mm]	Pipes, profiles: closed [mm]	Pipes, profiles: open [mm]	Aluminium [mm]	Sandwich materials [mm]	Glass fibre reinforced plastic/epoxy [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties							Ordering information							



T 121 GF



BIM, wavy set, milled
Very thin sheet metals, perforated sheet metals (0.5-1.5 mm)


0.5-1.5	-	-	0.5-1.5	-	-	92	0.8	2 608 636 695	C1b	3	10	596824	GAJ	9.54
								2 608 636 712	C1b	5	10	620352	GAJ	14.45
								2 608 636 697	P1a	25	1	596848	GAJ	61.42

Jigsaw blades – Speed for Metal

Fast, break proof and durable

speed  **Metal**


Sheet metals [mm]	Pipes, profiles: closed [mm]	Pipes, profiles: open [mm]	Aluminium [mm]	Sandwich materials [mm]	Glass fibre reinforced plastic/epoxy [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties							Ordering information							



T 121 AF

BIM, wavy set, milled
Thin sheet metals, perforated sheet metals (1-3 mm)


1-3	-	-	1-3	-	-	92	1.2	2 608 636 698	C1b	3	10	596855	GAJ	9.54
								2 608 636 713	C1b	5	10	620369	GAJ	14.45
								2 608 636 700	P1a	25	1	596947	GAJ	61.42



T 121 BF

BIM, wavy set, milled
Medium-thick sheet metals, perforated sheet metals (2.5-6 mm)


2.5-6	-	-	2.5-6	-	-	92	2.0	2 608 636 701	C1b	3	10	596954	GAJ	9.54
								2 608 636 714	C1b	5	10	620376	GAJ	14.45
								2 608 636 703	P1a	25	1	596978	GAJ	61.42



T 321 AF

BIM, wavy set, milled
Thin sheet metals, perforated sheet metals (1-3 mm), sandwich materials (<65 mm), thin-walled pipes, closed + open profiles, including aluminium (dia. <65 mm), glass fibre reinforced plastic/epoxy (<65 mm)

1-3	<65	<65	<65	<65	<65	132	1.2	2 608 636 704	C1b	3	10	596985	GAJ	14.50
								2 608 636 705	C1b	5	10	596992	GAJ	21.98



T 321 BF

BIM, side set, milled
Medium-thick sheet metals, perforated sheet metals (2.5-6 mm), sandwich materials (<65 mm), thick-walled pipes, closed + open profiles, including aluminium (dia. <65 mm), glass fibre reinforced plastic/epoxy (<65 mm)


2.5-6	<65	<65	<65	<65	<65	132	2.0	2 608 636 706	C1b	3	10	597005	GAJ	14.50
								2 608 636 707	C1b	5	10	597012	GAJ	21.98

Jigsaw blades – Flexible for Metal-Sandwich

Break proof and durable

flexible **for Metal-Sandwich**

Sandwich materials [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information						



T 718 BF



BIM, wavy set, milled
Sandwich materials (<120 mm)


<120	180	2	2 608 636 335	C1b	3	1	309042	GAJ	41.24
------	-----	---	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Progressor for Metal

Fast through thick and thin

PROGRESSOR **for Metal**

Sheet metals [mm]	Pipes profiles: closed [mm]	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information								



T 123 XF



HSS, side set, milled
Thin to thick sheet metals (1.5-10 mm), pipes + profiles, incl. aluminium (dia. <30 mm)


1.5-10	<30	<30	100	1.2-2.6	2 608 638 472	C1b	3	10	128049	GAJ	6.51
					2 608 638 473	C1b	5	10	128056	GAJ	10.40
					2 608 638 474	P1a	25	1	128063	GAJ	46.80
					2 608 638 700	C1a	100	1	264488	GAJ	176.80

Jigsaw blades – Basic for Inox

Good and cost-effective

basic **for INOX**

Inox sheets [mm]	Inox perforated sheets [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information							



T 118 GFS



BIM, wavy set, milled
Sawing in Inox / stainless steel


0.5-1.5	0.5-1.5	83	0.8	2 608 636 498	C1b	3	10	451864	GAJ	8.72
				2 608 636 496	C1b	5	10	451840	GAJ	13.45

Jigsaw blades – Basic for Inox

Good and cost-effective

basic for **INOX**

Inox sheets [mm]	Inox perforated sheets [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information						



T 118 EFS



BIM, wavy set, milled
Sawing in Inox / stainless steel


1.5-4	1.5-4	83	1.4	2 608 636 499	C1b	3	10	451871	GAJ	8.72
				2 608 636 497	C1b	5	10	451857	GAJ	13.45

Jigsaw blades – Special for Alu

Aluminium and non-ferrous metal

special for **Alu**

Sheet metals [mm]	Aluminium [mm]	Glass fibre reinforced plastic/epoxy [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information							



T 127 D



HSS, side set, milled
Thin to thick sheet metals (3-15 mm), pipes + profiles, (dia. <30 mm)

fast CUT

3-15	<30	<30	100	3	2 608 631 508	C1b	3	10	007405	GAJ	5.92
					2 608 631 017	C1b	5	10	007313	GAJ	9.21
					2 608 631 966	C1a	100	1	067515	GAJ	156.35



T 227 D



HSS, side set, milled
Thin to thick sheet metals (3-15 mm), pipes + profiles (dia. <30 mm), especially for curve cuts

fast CUT

3-15	<30	<30	100	3	2 608 631 671	C1b	3	10	007535	GAJ	7.83
					2 608 631 030	C1b	5	10	007320	GAJ	11.99
					2 608 638 382	C1a	100	1	279475	GAJ	203.81

Jigsaw blades

for special applications




Single lug shank

Jigsaw blades – Special for Inox

Stainless steel


special for **Inox**

Product properties		Ordering information							
Inox sheets [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat

T 118 AHM 

Tungsten carbide tipped (bar), ground
Thin, stainless steel sheets (Inox) (1.5-3 mm)

1.5-3	83	1.1	2 608 630 663	C1b	3	1	017749	GAJ	43.67
-------	----	-----	----------------------	-----	---	---	--------	-----	-------

T 118 EHM 

Tungsten carbide tipped (bar), ground
Medium-thick stainless steel sheets (Inox) (2-5 mm)


2-5	83	1.4	2 608 630 665	C1b	3	1	017756	GAJ	43.67
-----	----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Special for Synthetics

Abrasive synthetics

special for **Synthetics**

Product properties		Ordering information							
Glass fibre reinforced plastic/epoxy [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat

T 301 CHM 

Tungsten carbide tipped (bar), ground
Glass fibre reinforced plastic/epoxy, Corian (<65 mm)


<65	117	3.3	2 608 633 164	C1b	3	1	091824	GAJ	57.47
-----	-----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Special for Fiber and Plaster

Fibre and cement materials

special for **Fiber and Plaster**

Plasterboard	Porous concrete [mm]	Fibre cement [mm]	Glass fibre reinforced plastic/epoxy [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties						Ordering information						




T 141 HM



Tungsten carbide tipped, side set
Glass fibre reinforced plastic/epoxy (5-20 mm), plasterboard, fibre cement boards (5-50 mm)

5-50	-	5-50	5-20	100	4.3	2 608 633 175	C1b	3	1	109758	GAJ	36.44
------	---	------	------	-----	-----	---------------	-----	---	---	--------	-----	-------



T 341 HM



Tungsten carbide tipped, side set
Glass fibre reinforced plastic/epoxy (5-50 mm), plasterboard, fibre cement boards (<80 mm)


5-80	<80	5-80	5-50	132	4.3	2 608 633 176	C1b	3	1	109765	GAJ	42.24
------	-----	------	------	-----	-----	---------------	-----	---	---	--------	-----	-------

Jigsaw blades – Special for Ceramics

Ceramic materials

special for **Ceramics**

Ceramic wall tiles [mm]	Total length [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information			




T 130 RIFF



Tungsten carbide coated, with grit of 30
Soft ceramic wall tiles, cast iron (5-15 mm), coarse cut

5-15		83	2 608 633 104	C1b	3	1	035286	GAJ	17.98
------	--	----	---------------	-----	---	---	--------	-----	-------



T 150 RIFF



Tungsten carbide coated, with grit of 50
Soft ceramic wall tiles, cast iron (5-10 mm), fine cut

5-10		83	2 608 633 105	C1b	3	1	035293	GAJ	17.98
------	--	----	---------------	-----	---	---	--------	-----	-------

Jigsaw blades – Special for Acrylic

Acrylic glass

special for Acrylic

Perspex [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3163140...	Discount group	List Price ex vat
Product properties			Ordering information						



T 101 A



HSS, ground teeth and taper ground
Perspex, polycarbonate (2-20 mm)

2-20	100	2	2 608 631 670	C1b	3	1	007528	GAJ	11.04
			2 608 631 010	C1b	5	1	007276	GAJ	16.80

Jigsaw blades – Special for Soft Material

Soft materials

special for Soft-Material

Polystyrene, insulation [mm]	Cardboard, carpet, leather [mm]	Rubber [mm]	Total length [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3163140...	Discount group	List Price ex vat
Product properties			Ordering information							



T 113 A



HCS, ground blade
Cardboard, polystyrene, carpet, leather, rubber (<50 mm)

<50	<50	<50	100	2 608 635 177	C1b	3	1	035323	GAJ	8.89
-----	-----	-----	-----	---------------	-----	---	---	--------	-----	------




T 313 AW



HCS, blade with serrated edge
Cardboard, polystyrene, carpet, leather, rubber (<100 mm)

<100	<100	<100	152	2 608 635 187	C1b	3	1	045926	GAJ	10.22
------	------	------	-----	---------------	-----	---	---	--------	-----	-------

Jigsaw blades for wood




Universal shank

Jigsaw blades – Basic for Wood

Good and cost-effective

basic for Wood

Plywood [mm]	Softwood, panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3163140...	Discount group	List Price ex vat
Product properties				Ordering information						



U 19 BO



HCS, wavy set, milled
Softwood (2-15 mm), plywood, chipboard, wood core plywood, fibre boards, especially for curve cuts

2-15	2-15	70	2	2 608 630 567	C1b	3	1	007016	GAJ	3.05
------	------	----	---	---------------	-----	---	---	--------	-----	------



U 111 C



HCS, side set, milled
Softwood (4-50 mm), chipboards, wood core plywood, fibre boards

4-50	4-50	92	3	2 608 630 566	C1b	3	1	007009	GAJ	2.72
------	------	----	---	---------------	-----	---	---	--------	-----	------



U 111 D




HCS, side set, milled
Softwood (5-65 mm), chipboards, wood core plywood, fibre boards

5-65	5-65	92	4	2 608 637 559	C1b	3	1	014083	GAJ	2.97
------	------	----	---	---------------	-----	---	---	--------	-----	------


Jigsaw blades – Speed for Wood

Fast cut

speed for Wood



U 144 D



HCS, side set, ground
Softwood (5-50 mm), chipboards, wood core plywood, fibre boards


5-50	5-50	100	4-5.2	2 608 630 568	C1b	3	1	007023	GAJ	4.24
------	------	-----	-------	---------------	-----	---	---	--------	-----	------

Jigsaw blades – Clean for Wood

Clean cut



Plywood [mm]	Plastics [mm]	Softwood, panels [mm]	Laminated panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties						Ordering information						




U 1 AO



HCS, pointed teeth, ground teeth and taper ground
Softwood, plywood, laminated panels (1.5-15 mm), especially for curve cuts



1.5-15	-	1.5-15	1.5-15	70	1.4	2 608 637 724	C1b	3	1	038553	GAJ	5.14
--------	---	--------	--------	----	-----	---------------	-----	---	---	--------	-----	------




U 101 B



HCS, ground teeth and taper ground
Softwood, chipboard, wood core plywood, fibre boards (3-30 mm), plastics (3-30 mm)



-	3-30	3-30	-	100	2.7	2 608 630 565	C1b	3	1	006996	GAJ	5.51
---	------	------	---	-----	-----	---------------	-----	---	---	--------	-----	------



U 1 C



HCS, ground teeth and taper ground
Softwood (4-45 mm), chipboards, wood core plywood, fibre boards



-	-	4-45	-	80	3.0	2 608 637 560	C1b	3	1	014090	GAJ	5.51
---	---	------	---	----	-----	---------------	-----	---	---	--------	-----	------



U 101 D



HCS, ground teeth and taper ground
Softwood (10-45 mm), chipboards, wood core plywood, fibre boards




-	-	10-45	-	100	4-5.2	2 608 637 723	C1b	3	1	038546	GAJ	5.51
---	---	-------	---	-----	-------	---------------	-----	---	---	--------	-----	------

Jigsaw blades – Progressor for Wood

Fast and clean, through thick and thin



Softwood, panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information						



U 234 X




HCS, ground teeth and taper ground
Softwood (2-65 mm), chipboards, wood core plywood, fibre boards



2-65	108	2-3	2 608 633 525	C1b	3	1	169530	GAJ	9.11
------	-----	-----	---------------	-----	---	---	--------	-----	------

Jigsaw blades for hardwood




Universal shank

Jigsaw blades – Special for Laminate

Precise, clean cuts on both sides

special Laminate

Laminated panels [mm]	Multiplex panels [mm]	Laminates [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information						




U 1 BIF



BIM, ground teeth and taper ground
Laminates (1.5-15 mm), laminated panels/HPL (1.5-15 mm), multiplex panels (1.5-15 mm)

1.5-15	1.5-15	1.5-15	70	1.7	2 608 636 433	C1b	3	10	393430	GAJ	16.65
--------	--------	--------	----	-----	---------------	-----	---	----	--------	-----	-------




U 1 AOF



BIM, ground teeth and taper ground
Laminates (1.5-15 mm), laminated panels/HPL (1.5-15 mm), multiplex panels (1.5-15 mm)

1.5-15	1.5-15	1.5-15	70	1.4	2 608 636 462	C1b	3	10	414647	GAJ	15.04
--------	--------	--------	----	-----	---------------	-----	---	----	--------	-----	-------

Jigsaw blades for wood and metal




Universal shank

Jigsaw blades – Progressor for Wood and Metal

Universal, fast through thick and thin

PROGRESSOR

Construction timber with nails [mm]	Coarse wood [mm]	Glass fibre reinforced plastic/epoxy [mm]	Sheet metals, pipes, profiles [mm]	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information								




U 345 XF



BIM, side set, milled
Construction timber with nails (<65 mm), wooden materials, plastics, sheet metals, pipes/profiles, inc. aluminium (dia. 3-10 mm)

<65	<65	3-10	3-10	3-10	125	2.4-5	2 608 634 277	C1b	3	1	150491	GAJ	9.77
-----	-----	------	------	------	-----	-------	---------------	-----	---	---	--------	-----	------

Jigsaw blades for metal




Universal shank

Jigsaw blades – Basic for Metal

Good and cost-effective

basic for Metal

Product properties	Sheet metals [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
--------------------	-------------------	-------------------	--------------------	-------------	----------------	---------------	------------------------	--------------------	----------------	-------------------




U 118 G



HSS, wavy set, milled
Very thin sheet metals (0.5-1.5 mm)

0.5-1.5	70	0.7	2 608 631 770	C1b	3	1	014069	GAJ	4.83
---------	----	-----	----------------------	-----	---	---	--------	-----	------




U 118 A



HSS, wavy set, milled
Thin sheet metals (1-3 mm)

1-3	80	1.1-1.5	2 608 631 511	C1b	3	1	007412	GAJ	4.83
-----	----	---------	----------------------	-----	---	---	--------	-----	------



U 118 B




HSS, wavy set, milled
Medium-thick sheet metals (2.5-6 mm)

2.5-6	80	1.9-2.3	2 608 631 771	C1b	3	1	014076	GAJ	4.83
-------	----	---------	----------------------	-----	---	---	--------	-----	------

Jigsaw blades – Flexible for Metal

Breakproof and durable

flexible for Metal



U 118 BF



BIM, wavy set, milled
Medium-thick sheet metals, perforated sheet metals (2.5-6 mm)




2.5-6	80	1.9-2.3	2 608 634 695	C1b	3	1	038539	GAJ	6.28
-------	----	---------	----------------------	-----	---	---	--------	-----	------

Jigsaw blades – Progressor for Metal

Fast through thick and thin

PROGRESSOR for Metal

Sheet metals [mm]	Pipes, profiles: closed [mm]	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information							



U 123 XF 


HSS, side set, milled
Thin to thick sheet metals (1.5-10 mm), pipes + profiles, incl. aluminium (dia. <30 mm)

1.5-10	<30	<30	92	1.2-2.6	2 608 638 497	C1b	3	1	156677	GAJ	6.51
--------	-----	-----	----	---------	----------------------	-----	---	---	--------	-----	------

Jigsaw blades – Special for Alu

Aluminium and non-ferrous metal

special for Alu




U 127 D 

HSS, side set, milled
Thin to thick sheet metals (3-15 mm), pipes + profiles, (dia. <30 mm)

3-15	<30	<30	92	3	2 608 631 512	C1b	3	1	007429	GAJ	4.85
------	-----	-----	----	---	----------------------	-----	---	---	--------	-----	------

Jigsaw blades for special applications




Universal shank

Jigsaw blades – Special for Ceramics

Ceramic materials

special for Ceramics

Ceramic wall tiles [mm]	Total length [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties		Ordering information						




U 30 RIFF 

Tungsten carbide coated
Soft ceramic wall tiles, cast iron (5-15 mm), coarse cut

5-15	70	2 608 633 106	C1b	3	1	038515	GAJ	15.58
------	----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades

for wood



Makita shank

Jigsaw blades – Basic for Wood

Good and cost-effective
basic for Wood

Softwood, panels [mm]	Plywood [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3163140...	Discount group	List Price ex vat
Product properties				Ordering information						



MA 119 HO



HCS, side set, milled

Softwood (3-15 mm), plywood, chipboard, wood core plywood, fibre boards, especially for curve cuts

3-15	3-15	80	2.5	2 608 633 501	C1b	5	1	184755	GAJ	12.10
------	------	----	-----	---------------	-----	---	---	--------	-----	-------



MA 111 C



HCS, side set, milled

Softwood (4-50 mm), chipboards, wood core plywood, fibre boards

4-50	-	80	3.0	2 608 637 572	C1b	5	1	014519	GAJ	4.92
------	---	----	-----	---------------	-----	---	---	--------	-----	------



MA 111 D



HCS, side set, milled

Softwood (5-65 mm), chipboards, wood core plywood, fibre boards

5-65	-	80	4.0	2 608 633 500	C1b	5	1	184748	GAJ	11.07
------	---	----	-----	---------------	-----	---	---	--------	-----	-------

Jigsaw blades – Clean for Wood

Clean cut



Softwood, panels [mm]	Plastics [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information						



MA 101 BC



HCS, ground teeth and taper ground
Softwood, chipboard, wood core plywood, fibre boards, plastics (3-30 mm)


3-30	3-30	80	2.7	2 608 633 502	C1b	5	1	184762	GAJ	12.82
------	------	----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Progressor for Wood

Fast, clean, through thick and thin



Softwood, panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information						




MA 234 X



HCS, ground teeth and taper ground
Softwood (2-65 mm), chipboards, wood core plywood, fibre boards

2-65	110	2-3	2 608 633 530	C1b	5	1	169547	GAJ	13.03
------	-----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades for wood and metal




Makita shank

Jigsaw blades – Progressor for Wood and Metal

Universal, fast through thick and thin



Construction timber with nails [mm]	Coarse wood [mm]	Glass fibre reinforced plastic/epoxy [mm]	Sheet metals, pipes, profiles [mm]	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties					Ordering information								




MA 345 XF



BIM, side set, milled
Construction timber with nails (<65 mm), wooden materials, glass fibre reinforced plastic/epoxy, sheet metals, pipes/profiles, including aluminium (dia. 3-10 mm)

<65	<65	3-10	3-10	3-10	120	2.4-5	2 608 634 278	C1b	5	1	150507	GAJ	15.63
-----	-----	------	------	------	-----	-------	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades for metal




Makita shank

Jigsaw blades – Basic for Metal

Good and cost-effective

basic for Metal



MA 118 A



HSS, wavy set, milled
Thin sheet metals (1-3 mm)

1-3	80	1.1	2 608 631 781	C1b	5	1	014533	GAJ	8.03
-----	----	-----	---------------	-----	---	---	--------	-----	------




MA 118 B



HSS, wavy set, milled
Medium-thick sheet metals (2.5-6 mm)

2.5-6	80	1.8	2 608 631 780	C1b	5	1	014526	GAJ	8.03
-------	----	-----	---------------	-----	---	---	--------	-----	------



MA 118 H




HSS, side set, milled
Thick sheet metals (3-8 mm)

3-8	80	2.5	2 608 631 782	C1b	5	1	014540	GAJ	8.03
-----	----	-----	---------------	-----	---	---	--------	-----	------

Jigsaw blades – Flexible for Metal

Breakproof and durable

flexible for Metal




MA 18 AF



BIM, wavy set, milled
Thin sheet metals, perforated sheet metals (1-3 mm)



1-3	80	1.1	2 608 634 296	C1b	5	1	184793	GAJ	18.87
-----	----	-----	---------------	-----	---	---	--------	-----	-------



MA 18 BF



BIM, wavy set, milled
Medium-thick sheet metals, perforated sheet metals (2.5-6 mm)



2.5-6	80	1.8	2 608 634 297	C1b	5	1	184809	GAJ	18.87
-------	----	-----	---------------	-----	---	---	--------	-----	-------

Jigsaw blades – Flexible for Metal

Breakproof and durable

flexible for **Metal**

Sheet metals [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information						



MA 18 BOF



BIM, side set, milled

Medium-thick sheet metals, perforated sheet metals (2-6 mm), especially for curve cuts



2-6	80	1.8	2 608 634 295	C1b	5	1	184779	GAJ	22.25
-----	----	-----	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Progressor for Metal

Fast through thick and thin

PROGRESSOR for **Metal**

Sheet metals [mm]	Pipes Profiles: closed [mm]	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information								



MA 123 X



HSS, side set, milled

Thin to thick sheet metals (1.5-10 mm), pipes + profiles, incl. aluminium (dia. <30 mm)



1.5-10	<30	<30	95	1.2-2.6	2 608 638 498	C1b	5	1	156691	GAJ	10.40
--------	-----	-----	----	---------	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades – Special for Alu

Aluminium and non-ferrous metal

special for **Alu**



MA 127 D



HSS, side set, milled

Thin to thick sheet metals (3-15 mm), pipes + profiles, (dia. <30 mm)



3-15	<30	<30	80	3	2 608 638 511	C1b	5	1	184786	GAJ	14.56
------	-----	-----	----	---	----------------------	-----	---	---	--------	-----	-------

Jigsaw blades for wood




Double lug shank

Jigsaw blades – Basic for Wood

Good and cost-effective

Product properties					Ordering information						
Softwood, panels [mm]	Plywood [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3163140...	Discount group	List Price ex vat	



T 19 BO



HCS, wavy set, milled
Softwood (2-15 mm), plywood, chipboard, wood core plywood, fibre boards, especially for curve cuts

2-15	2-15	85	2	2 608 630 309	C1b	5	1	006934	GAJ	5.89
------	------	----	---	----------------------	-----	---	---	--------	-----	------



T 57 C



HCS, side set, milled
Softwood (4-50 mm), chipboards, wood core plywood, fibre boards

4-50	-	96	3	2 608 630 061	C1b	5	1	006866	GAJ	5.26
------	---	----	---	----------------------	-----	---	---	--------	-----	------

Jigsaw blades – Speed for Wood

Fast cut

Product properties					Ordering information						
Softwood, panels [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3163140...	Discount group	List Price ex vat		



T 44 D



HCS, side set, ground
Softwood (5-50 mm), chipboards, wood core plywood, fibre boards



5-50	96	4	2 608 630 010	C1b	5	1	006774	GAJ	6.95
------	----	---	----------------------	-----	---	---	--------	-----	------

Jigsaw blades – Clean for Wood

Clean cut



Softwood, panels [mm]	Plastics [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties				Ordering information						



T 1 B



HCS, ground teeth and taper ground
 Softwood, chipboard, wood core plywood, fibre boards, plastics (3-30 mm)



3-30	3-30	96	2.5	2 608 630 000	C1b	5	1	006750	GAJ	8.48
------	------	----	-----	---------------	-----	---	---	--------	-----	------



Jigsaw blades for metal




Double lug shank

Jigsaw blades – Basic for Metal

Good and cost-effective

basic for Metal

Sheet metals [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information						



T 18 A



HSS, wavy set, milled
Thin sheet metals (1-3 mm)


1-3	85	1.2	2 608 631 002	C1b	5	1	007269	GAJ	8.90
-----	----	-----	---------------	-----	---	---	--------	-----	------

Jigsaw blades – Special for Alu

Aluminium and non-ferrous metal

special for Alu

Sheet metals [mm]	Pipes [mm], profiles: closed	Aluminium [mm]	Total length [mm]	Tooth spacing [mm]	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
Product properties			Ordering information								



T 27 D




HSS, side set, milled
Thin to thick sheet metals (3-15 mm), pipes + profiles, (dia. <30 mm)

fast CUT

3-15	<30	<30	96	3	2 608 630 008	C1b	5	1	006767	GAJ	9.47
------	-----	-----	----	---	---------------	-----	---	---	--------	-----	------

Jigsaw blade sets

3-piece jigsaw blade sets (single lug shank)



3-piece jigsaw blade set
 Universal, fast through thick and thin
 For wood, plastic and metal

T 123 XF Progressor for Metal	2 607 010 515	C1b	1	1	198868	GAJ	8.46
T 234 X Progressor for Wood			1				
T 345 XF Progressor for Wood and Metal			1				

3-piece jigsaw blade set
 For wood, plastic and metal

T 111 C Basic for Wood	2 607 010 062	C1b	1	1	006644	GAJ	5.01
T 244 D Speed for Wood			1				
T 118 B Basic for Metal			1				

3-piece jigsaw blade set
 Precise, clean cuts in laminate

T 101 BIF Special for Laminate	2 608 636 429	C1b	2	1	393393	GAJ	13.84
T 101 AOF Special for Laminate			1				

3-piece jigsaw blade set
 For softwood and non-abrasive wooden materials

T 308 B Extraclean for Wood	2 607 010 592	C1b	2	1	535830	GAJ	7.29
T 308 BO Extraclean for Wood			1				

3-piece jigsaw blade set
 For hardwood and abrasive wooden materials

T 308 BF Extraclean for Hard Wood	2 607 010 593	C1b	2	1	535847	GAJ	12.74
T 308 BOF Extraclean for Hard Wood			1				

3-piece jigsaw blade sets (universal shank)



3-piece jigsaw blade set
 Universal, fast through thick and thin
 For wood, plastic and metal

U 123 XF Progressor for Metal	2 607 010 516	C1b	1	1	198875	GAJ	8.46
U 234 X Progressor for Wood			1				
U 345 XF Progressor for Wood and Metal			1				

3-piece jigsaw blade set
 Precise, clean cuts in laminate

U 1 BIF Special for Laminate	2 608 636 430	C1b	2	1	393409	GAJ	15.04
U 1 AOF Special for Laminate			1				

Robust Line 6-piece jigsaw blade sets (single lug shank)



Set size A:
157 x 70 x 23 mm

Product properties	Ordering information
--------------------	----------------------

6-piece Robust Line jigsaw blade set Progressor

Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
T 123 XF Progressor for Metal	A	2 607 010 531	P1k	2	1	446150	GRL	15.33
T 234 X Progressor for Wood				2				
T 345 XF Progressor for Wood and Metal				2				

6-piece Robust Line jigsaw blade set Wood Expert

T 308 B Extraclean for Wood	A	2 607 010 572	P1k	1	1	475976	GRL	15.33
T 308 BF Extraclean for Hard Wood				1				
T 301 BCP Precision for Wood				2				
T 234 X Progressor for Wood				2				

6-piece Robust Line jigsaw blade set Metal Profile

T 318 AF Flexible for Metal	A	2 607 010 573	P1k	2	1	475983	GRL	15.79
T 318 BF Flexible for Metal				2				
T 345 XF Progressor for Wood and Metal				2				

Robust Line 6-piece jigsaw blade sets (universal shank)



Set size A:
157 x 70 x 23 mm

6-piece Robust Line jigsaw blade set Progressor

U 123 XF Progressor for Metal	A	2 607 010 532	P1k	2	1	446167	GRL	15.33
U 234 X Progressor for Wood				2				
U 345 XF Progressor for Wood and Metal				2				

Robust Line 10-piece jigsaw blade sets (single lug shank)



Set size C:
124 x 107 x 23 mm

10-piece Robust Line jigsaw blade set Wood Expert

T 101 AO Clean for Wood	C	2 607 010 540	P1k	1	1	446242	GRL	16.72
T 101 B Clean for Wood				1				
T 101 BR Clean for Wood				1				
T 101 AOF Clean for Hard Wood				1				
T 101 BF Clean for Hard Wood				1				
T 101 BRF Clean for Hard Wood				1				
T 244 D Speed for Wood				1				
T 144 D Speed for Wood				1				
T 144 DF Speed for Hard Wood				1				
T 144 DP Precision for Wood				1				



Set size C:
124 x 107 x 23 mm

10-piece Robust Line jigsaw blade set Metal Expert

T 118 G Basic for Metal	C	2 607 010 541	P1k	1	1	446259	GRL	18.57
T 118 A Basic for Metal				1				
T 118 B Basic for Metal				1				
T 118 EOF Flexible for Metal				1				
T 118 AF Flexible for Metal				1				
T 118 BF Flexible for Metal				1				
T 118 GFS Basic for Inox				1				
T 227 D Special for Alu				1				
T 127 D Special for Alu				1				
T 123 XF Progressor for Metal				1				

Robust Line 10-piece jigsaw blade sets (single lug shank)

Product properties		Ordering information						
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
10-piece Robust Line jigsaw blade set Wood and Metal								
T 244 D Speed for Wood	C	2 607 010 542	P1k	1	1	446266	GRL	16.25
T 144 D Speed for Wood								
T 101 AO Clean for Wood								
T 101 B Clean for Wood								
T 101 AOF Clean for Hard Wood								
T 101 BF Clean for Hard Wood								
T 118 EOF Flexible for Metal								
T 118 AF Flexible for Metal								
T 118 BF Flexible for Metal								
T 123 XF Progressor for Metal								



Set size C:
124 x 107 x 23 mm

Product properties		Ordering information						
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
10-piece Robust Line jigsaw blade set Top Expert								
T 130 RIFF Special for Ceramics	C	2 607 010 574	P1k	1	1	475990	GRL	24.62
T 118 AHM Special for Inox								
T 141 HM Special for Fiber and Plaster								
T 101 A Special for Acrylic								
T 113 A Special for Soft Material								
T 101 BF Clean for Hard Wood								
T 101 BIF Special for Laminate								
T 118 AF Flexible for Metal								
T 227 D Special for Alu								
T 123 XF Progressor for Metal								

10-piece jigsaw blade sets (single lug shank)



Product properties		Ordering information						
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
10-piece jigsaw blade set Wood Basic								
T 119 B0 Basic for Wood		2 607 010 629	P1k	2	1	579353	GAZ	11.70
T 119 B Basic for Wood								
T 111 C Basic for Wood								



Product properties		Ordering information						
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
10-piece jigsaw blade set Wood/Metal Basic								
T 119 B0 Basic for Wood		2 607 010 630	P1k	2	1	579360	GAZ	14.93
T 119 B Basic for Wood								
T 111 C Basic for Wood								
T 218 A Basic for Metal								
T 118 G Basic for Metal								
T 118 A Basic for Metal								
T 118 B Basic for Metal								



Product properties		Ordering information						
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
10-piece jigsaw blade set Metal Basic								
T 218 A Basic for Metal		2 607 010 631	P1k	2	1	579377	GAZ	20.26
T 118 G Basic for Metal								
T 118 A Basic for Metal								
T 118 B Basic for Metal								

Accessories for jigsaws

Anti-splinter guard for jigsaws

- The anti-splinter guard effectively prevents tearing out on the top of the material. All you have to do is insert it into the sole plate. Another **tip**: It is best to saw with or diagonal to the grain



Product properties	Ordering information						
	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode	Discount group	List Price ex vat
Anti-splinter guard Appropriate for GST 14,4 V; GST 18 V; GST 75 BE; GST 80 Professional; PST 650; PST 650 L; PST 680 E; PST 680 EL; PST 700 PE; PST 800 PEL; PST 900 PEL; PST 1000 CE	2 607 010 079	C1d	5	5	006651	GAT	4.09



Anti-splinter guard Appropriate for GST BCE; GST 150 CE Professional	2 601 016 096	P1d	5	5	516297	GAT	4.89
--	---------------	-----	---	---	--------	-----	------

Plastic plate for sole plate for jigsaws

- The interchangeable plastic plate ensures good movement on different materials



Plastic plate for sole plate Appropriate for PST 700 PAE; PST 800 PAC	2 601 099 040	P1d	1	1	073851	GAT	8.06
---	---------------	-----	---	---	--------	-----	------

Dust extraction



Dust extraction set Appropriate for GST BCE; GST 150 CE Professional	2 605 510 294	P1d	1	1	516280	GAT	7.36
--	---------------	-----	---	---	--------	-----	------

Parallel guide with circle cutter

Product properties	Ordering information
	Part number Packaging type Pack quantity Minimum order quantity Barcode 3165140... Discount group List Price ex vat



Parallel guide with circle cutter

Appropriate for GST 14,4 V; GST 18 V; GST 24 V; GST 75 BE; GST 120 E; GST 135 BCE; GST 135 CE; GST 150 BCE; GST 150 CE Professional; PST 650; PST 650 L; PST 680 E; PST 680 EL; PST 700 E; PST 700 PE; PST 800 PEL; PST 900 PEL; PST 1000 CE; PST 1000 PEL

2 608 040 289	P1d	1	1	516273	GAT	11.12
---------------	-----	---	---	--------	-----	-------

Universal cutting oil and screwdriver

- Universal cutting oil in a spray can increases the lifetime of the tool by up to +30%, whilst also increasing the cutting speed



Universal cutting oil

Using the universal cutting oil increases the lifetime several times over when cutting in metal

2 607 001 409	M0b	1	1	271240	GAT	6.77
---------------	-----	---	---	--------	-----	------

Screwdriver

Appropriate for all jigsaws without SDS system



1 609 200 265	C1d	1	1	004497	GAT	2.91
---------------	-----	---	---	--------	-----	------