

Datasheet

RS Pro Thermoplastic Knob, M6 x 9

RS Stock No: **702-7651**



Product Details

RS Pro thermoplastic knob in black colour, features M6 x 9 thread size, zinc plated steel, brass or stainless steel inserts. It is resistant to most chemicals, UV light and water absorption.

Features and Benefits

- Resistant to most chemicals, UV light and water absorption (1.5% maximum)
- Temperature range: -20 to +110°C (short term withstand +170°C)
- PP construction



ENGLISH

Specifications:

Body Material	PP
Colour	Black
Insert Material	Stainless Steel
Knob Diameter	28 mm
Knob Shape	Multiple Lobes
Mounting Type	Threaded Hole
Thread Diameter	M6
Thread Length	9 mm
Thread	M6 x 9
Operating Temperature Range	-20 to +110°C