


## **Common Mode Choke**

**TCK-048** 


Order Code	TCK-048
Inductance (each winding)	<b>450 μH ±35%</b> (at 100 kHz / 100 mV)
Impedance (DCR)	25 mΩ max.
Rated Current	5.2 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +125°C



## Impedance Curve



## **Outline Dimensions**



Dimensions [mm]	
Α	11.5 max.
В	11.5 max.
С	9.8 max.
D	2.5 min.
E	7.62 ±0.2
F	7.62 ±0.2
G	ø 0.6 ±0.1

© Copyright 2020 Traco Electronic AG

Specifications can be changed without notice.