



DCF921P2T-GB – 18V XR Brushless 1/2" Hog Ring Compact Impact Wrench - 2 X 5AH in TSTAK



The DCF921 18V XR Impact Wrench with Hog Ring Anvil was designed to easily handle various fastening projects. Get up to 406Nm of fastening torque and 610Nm of max breakaway torque in a 125mm long body with this compact power tool that offers easy maneuverability without sacrificing power. Choose between 4 modes to allow for reliable high-level performance, operability, and versatility. Dark work areas are no problem with this Cordless Impact Wrench, which comes with an LED work light for visibility in dimly lit spaces.

Features and Benefits:

- 406Nm of Fastening Torque
- 610Nm of Breakaway Torque
- Compact 125mm Head Length
- Brushless Motor
- 4 Mode Switch for Accurate Application Control
- Scaffold Mode offers excellent application control for Scaffolders
- 1/2"" Anvil with Hog Ring

Specifications:

- Power Source Cordless
- Voltage 18V
- Breakaway Torque 609 Nm
- Fastening Torque 406 Nm
- Speed 2 speed Variable and Reverse
- No Load Speed 0 2500 Rpm
- Hand/Arm Vibration Impact 13 m/s²
- Uncertainty K 1 (Vibration) 1.5 m/s²
- Sound Pressure 97 dB(A)
- Sound Pressure Uncertainty 3 dB(A)
- Sound Power 108 dB(A)

Supplied with:

- DCF921 ½" Impact Wrench
- 2 x 5.0Ah Batteries (DCB184-XJ)
- Multi Voltage Charger
- T-Stak Kit Box